

Forix™

IP 2X surface-mounting switches and socket outlets



7 824 00



7 824 02



7 824 20

Conform to IEC standard
 Complete mechanisms supplied with rocker and cover plate - Screw terminals IP2X
 2 finishes:
 - White RAL R903 - Glossy finish
 - Ivory RAL R113 - Glossy finish

Pack	Cat.Nos	Switches 10 AX - 250 V~
20 20	7 824 00 7 824 30	Become illuminated with LED lamp Cat. No. 7 824 57 One-way switches ○ White ● Ivory
20 20	7 824 04 7 824 34	Two-way switches ○ White ● Ivory
20 20	7 824 02 7 824 32	2 gang one-way switches ○ White ● Ivory
20 20	7 824 06 7 824 36	2 gang two-way switches ○ White ● Ivory
20 20	7 824 05 7 824 35	Push-buttons 6 A - 250 V~ Become illuminated with LED lamp Cat. No. 7 824 57 ○ White ● Ivory

Pack	Cat.Nos	2P socket outlets 16 A - 250 V~
20 20	7 824 10 7 824 40	2P without shutters ○ White ● Ivory
10 10	7 824 12 7 824 42	2 x 2P without shutters ○ White ● Ivory
20 20	7 824 11 7 824 41	German standard socket outlets 16 A - 250 V~ 2P+E without shutters ○ White ● Ivory
10 10	7 824 13 7 824 43	2 x 2P+E without shutters Inclined 45° - Horizontal or vertical mounting ○ White ● Ivory
20 20	7 824 20 7 824 50	2P+E with shutters ○ White ● Ivory
10 10	7 824 23 7 824 53	2 x 2P+E with shutters Inclined 45° - Horizontal or vertical mounting ○ White ● Ivory
10 10	7 824 18 7 824 48	3 x 2P+E with shutters ○ White ● Ivory
10 10	7 824 19 7 824 49	French standard socket outlets 16 A - 250 V~ 2 x 2P+E with shutters ○ White ● Ivory

