

## Plexo™ complete surface mounting IP 55 - switches and push-buttons



0 697 61L

0 697 22L

Mechanisms supplied complete with non-clipped frame

Pack	Cat.Nos	Switches 10 AX - 250 V~
10	0 697 11L	IP 55 - IK 08. Automatic terminals <b>Two-way switch</b> ● Grey ● Anthracite
10	0 697 61L	
10	0 697 12L	<b>Two-way switch - with indicator</b> Supplied with 230 V~ lamp to be wired with a terminal block ● Grey ● Anthracite
10	0 697 21L	
10	0 697 13L	<b>Illuminated two-way switch</b> Supplied with 230 V~ lamp to be wired ● Grey ● Anthracite
10	0 697 36L	
5	0 697 16L	<b>Intermediate switch</b> ● Grey
10	0 697 15L	<b>2-gang switch/push-button - 10 AX - 250 V~</b> IP 55 - IK 08. Automatic terminals Supplied as a 2-gang push-button Allows to create 3 functions: - 2-gang two-way switch - 2-gang changeover push-button - two-way switch + changeover push-button ● Grey ● Anthracite
10	0 697 75L	
10	0 697 20L	<b>Push-buttons 10 A</b> IP 55 - IK 08. Automatic terminals <b>NO contact push-button</b> ● Grey ● Anthracite
10	0 697 90L	
10	0 697 22L	<b>Illuminated NO contact push-button</b> Supplied with 230 V~ lamp to be wired ● Grey ● Anthracite
10	0 697 82L	

## Plexo™ complete surface mounting IP 55 motion sensors



0 697 40

Mechanisms supplied complete with non-clipped frame

Pack	Cat.Nos	Motion sensor
1	0 697 40	IP 55 - IK 04 - 3-wire with neutral Automatic terminals Allows control of a lighting device as soon as the movement is detected Maximum load: - 2000 W for incandescent, halogen 230 V and halogen 12 V lamps, - 1000 VA for fluorescent tubes and compact fluorescent lamps Temporization between 12 s and 16 min. Detection angle: 360° Light level threshold : 5 à 1275 lux Detection range from 0 to 12 m with detector installed on wall at a height of 2.50 m. Minimum installation height: 1.70 m With directional head, can be removed without tools Dim. 90 x 91 mm (diameter: 91 mm) ● Grey ○ White ○ White - retail packaging
1	0 697 80	
1	0 488 98	