

# Plexo™ complete surface mounting IP 55

## socket outlets



0 697 83L



0 697 32L



0 697 31L



0 916 55



0 558 77

IP 55 - IK 08. Mechanisms supplied complete with non-clipped frame

Pack	Cat.Nos	German standard socket outlet - 16 A - 250 V~
		With shutters for child protection Supplied with 1 membrane gland - 2 outputs <b>2P+E socket outlets - screw terminals</b>
10	0 697 33L	<ul style="list-style-type: none"> <li>● Grey</li> <li>● Anthracite</li> </ul>
10	0 697 83L	
		<b>British standard socket outlets - 13 A - 250 V~</b>
		<b>Socket outlets - screw terminals</b>
10	0 697 32L	● 2P+E - Grey
5	0 697 39L	● 2 x 2P+E - Grey
5	0 697 50L	● 2P+E + 2-way switch - Grey
		<b>French standard socket outlet - 16 A - 250 V~</b>
		With shutters for child protection Supplied with 1 membrane gland - 2 outputs <b>2P+E socket outlets - automatic terminals</b>
10	0 697 31L	● Grey

Pack	Cat.Nos	Socket outlets 20 A and 32 A
		Screw terminals ● Grey
		<b>20 A</b> Compatible with membrane gland Cat.No 0 919 14
5	0 916 55	2P+E - 230 V~
5	0 916 56	3P+E - 400 V~
5	0 916 57	3P+N+E - 400 V~
		<b>32 A</b> Compatible with membrane gland Cat.No 0 919 15
5	0 558 72	2P+E - 230 V~
5	0 558 75	3P+E - 230 V~
5	0 558 77	3P+N+E - 230 V~
		<b>Membrane glands with marking of Ø for tubes and cables</b>
50	0 919 14	● Grey (RAL 7035) Up to Ø20
50	0 919 15	Up to Ø25