

Plexo™ mechanisms IP 55 - surface mounting boxes and flush-mounting support frames



To be equipped with modular Plexo mechanisms (p. 792 to 794)

Pack	Cat.Nos	
		1-gang surface mounting box with membrane glands
		Equipped with removable membrane glands
10	0 696 51L	2 membrane glands 1 entry
10	0 696 01L	● Grey
10	0 696 89L	● Anthracite
		○ White
		2-gang and 3-gang surface mounting box with membrane glands
		No separation between compartments in order to facilitate the cabling operations and to allow the installation of prewired socket outlets
		2-gang - horizontal or vertical mounting
		3 membrane glands 1 entry
		1 membrane gland 2 entries
5	0 696 72L	● Grey
5	0 696 02L	● Anthracite
5	0 696 90L	○ White
		3-gang - horizontal or vertical mounting
		4 membrane glands 1 entry
		1 membrane gland 2 entries
5	0 696 80L	● Grey
5	0 696 03L	● Anthracite
5	0 696 88L	○ White
		Surface mounting boxes for cable glands
		1-gang, 1 entry - ISO 20
10	0 696 56L	● Grey
		2-gang, 2 entries - ISO 20
		For horizontal or vertical mounting
		The 2-entry cable gland can be positioned at different locations
5	0 696 68L	● Grey
		Flush-mounting support frames
		Used for flush-mounting version for German and French standard boxes only
		1-gang
		Can be equipped with claws Cat.Nos 0 697 96L/97L
10	0 696 81L	● Grey
10	0 696 06L	● Anthracite
10	0 696 92L	○ White
		2-gang - horizontal or vertical mounting
		71 mm fixing centers
5	0 696 83L	● Grey
5	0 696 07L	● Anthracite
5	0 696 94L	○ White
		Claws
		Sets of 2 claws + 1 spacer
50	0 697 96L	Standard claws
25	0 697 97L	Long claws

Plexo™ mechanisms IP 55 membrane glands, cable glands and accessories



Pack	Cat.Nos	
		Membrane glands
		1 entry - Ø up to 25 mm
10	0 695 96L	● Grey
		2 entries - Ø up to 12.5 mm
10	0 695 99L	● Grey
		For pairing
		Allows to combine surface mounting boxes with one another
10	0 696 65L	● Grey
		Cable glands
		For installation in place of a membrane gland
		1 entry ISO 20
10	0 696 60L	● Grey
10	0 696 63L	● Anthracite
10	0 696 62L	○ White
		2 entries ISO 20
10	0 696 70L	● Grey
10	0 696 73L	● Anthracite
10	0 696 71L	○ White
		Lamps to be wired
5	0 694 96L	230 V~ - 0.2 mA - blue - locator
5	0 694 98L	230 V~ - 2 mA - blue - indicator
5	0 694 95L	12 to 48 V~ - 2.6 mA (48 V~) - blue
		Fixing accessories
		1-gang stainless steel height spacer for sandwich panel
		Supplied with screw for fixing the product on the height spacer and double insulated caps (Class II) for the wiring accessory
5	0 694 92L	
		For thin walls
		Does not require a flush-mounting box
10	0 695 97L	
		Set of 4 caps
		For sealing fixing holes when installing a surface mounting box on a metal support
10	0 695 98L	● Grey