

Plexo™ boxes IP 55 - IK 07

with direct entry membrane glands - 750 °C



0 920 32

0 920 52

Dimensions **p. 804**
Technical characteristics **p. 805**

Resistance to glow wire test: 750 °C (EN 60695 2-11)
Operating temperature: - 25 °C to + 40 °C
Interchangeable membrane glands with direct entry
Captive cover with clippable tie between box and cover except boxes 310 x 240 and 360 x 270
Cover opens/closes with a 1/4 turn of a regular screwdriver, marking 0 and I
Class II is ensured by protection caps (supplied) for the attachment screws
Can be associated with Nybloc auto terminal support Cat.No 0 343 98

Pack	Cat.Nos	Square boxes
1	0 920 32	Grey RAL 7035 130 x 130 x 74 mm 10 glands Ø cables and tubes accepted 4 to 25 mm
Rectangular boxes		
20	0 920 42	Grey RAL 7035 155 x 110 x 74 mm 10 glands Ø cables and tubes accepted 4 to 25 mm
10	0 920 52	180 x 140 x 86 mm 10 glands Ø cables and tubes accepted 4 to 32 mm
10	0 920 62	220 x 170 x 86 mm 14 glands Ø cables and tubes accepted 4 to 32 mm
2	0 920 82	310 x 240 x 124 mm 24 glands Ø cables and tubes accepted 4 to 40 mm
1	0 920 92	360 x 270 x 124 mm 24 glands Ø cables and tubes accepted 4 to 40 mm

Plexo™ boxes IP 55 - IK 07

with direct entry membrane glands - 960 °C



0 920 15

Dimensions **p. 804**
Technical characteristics **p. 805**

Resistance to incandescent wire: 960°C
Junction boxes for safety circuit installations in buildings open to the public and work premises
Operating temperature: -25 to +40°C
Interchangeable membrane glands with direct entry for IRL tubes up to Ø16 and R02V cables. Marked cut-out for IRL tubes Ø >16
Captive cover with clippable tie between box and cover
Space for marking on both sides of the cover of 80 x 80 and 105 x 105 boxes
Fixing with vertical level adjustment
Class II is ensured by protective caps (supplied) for the fixing screws

Pack	Cat.Nos	Square boxes
10	0 920 15	Grey/red RAL 7037/3000 80 x 80 x 45 mm Clippable covers 7 membrane glands (Cat.No 0 919 09) Accepted cable and tube Ø: 4 to 20 mm
10	0 920 25	105 x 105 x 55 mm Cover closed with a 1/4 turn Fixed using 2 internal points (screws with max. Ø5 mm) or 3 points outside the wiring space (screws with max. Ø4 mm) 7 membrane glands (Cat.No 0 919 01) Accepted cable and tube Ø: 4 to 25 mm

Nybloc auto terminal support
p. 819

