Plastic industrial boxes

Can be equipped with a rail for fixing equipment

Hinges Cat.No 0 358 01

Wall mounting lugs Cat.No 0 358 02 for horizontal or vertical installation



0 359 71

IP 2X terminal blocks fixed at the top from 130 x 130 mm

Technical characteristics **p. 808**

Smooth surfaces
Choice of fixing:
- Internal: 4 oblong holes at back of box
- At the 4 corners outside the wiring space, with Ø4 screws
- Using wall mounting lugs Cat.No 0 358 02 (except boxes 130 x 75 x 74 mm)

IP 55 - IK 07 grey RAL 7035

Class II provided by protective caps for the fixing screws (supplied)
Equipment can be fixed on rail or solid plate
IP 2X terminal blocks fixed at the top from 130 x 130 mm size (p. 298)
Cover opened/closed with 1/4 turn of a flat screwdriver. Indication of closed/open position: I/O
Captive covers with ties, except boxes 310 x 240 mm and 360 x 270 mm

Pack	Cat.Nos		Internal dimensions Height x Width x Depth (mm)
	Opaque cover	Transparent cover	
1	0 359 00		141 x 86 x 80
1	0 359 30		150 x 150 x 81
1	0 359 40		175 x 130 x 81
1	0 359 50		200 x 160 x 94
1	0 359 60	0 359 61	240 x 190 x 94
1	0 359 70	0 359 71	290 x 190 x 94
1	0 359 80		382 x 292 x 132

IP 55 - grey RAL 7035 - increased depth

Pack	Cat.Nos	
	Opaque cover	
		Box depth 140 mm IK 07
2	0 921 22	220 x 170 x 240 mm with 4 locks
		Box depth 154 mm IK 08
1	0 350 58	359 x 265 x 154 mm with hinges and 2 locks
		Box depth 160 mm IK 08
1	0 922 84	310 x 240 x 160 mm with 4 locks

Accessories for IP 55 - IK 07 grey RAL 7035

Pack	Cat.Nos	
		Hinges RAL 7016 - set of 2
1	0 358 00	For boxes 130 x 130 up to 270 x 170 mm included
1	0 358 01	For boxes 310 x 240 mm and 360 x 270 mm
		Metal mounting plates Galvanized steel 15/10 thick
5	0 358 10	For boxes 150 x 150 mm
5	0 358 11	For boxes 175 x 130 mm
5	0 358 12	For boxes 200 x 160 mm
5	0 358 13	For boxes 240 x 190 mm
5	0 358 14	For boxes 290 x 190 mm
10	0 358 15	For boxes 382 x 292 mm
		Wall mounting lugs
1	0 358 02	Set of 4 lugs for boxes from width 110 mm For wall fixing supplied with screws

Weatherproof cabinets, **p. 416**