

Batibox™

flush-mounting boxes for dry partitions



Installation p. 811

Pack	Cat.Nos	1-gang boxes	Pack	Cat.Nos	Junction boxes
20	Depth 40 0 800 40	For 1 module Drilling diameter 32 mm			Supplied with cover and screws Knockout base
50	0 800 41 Depth 50 0 800 51	For 1 gang or 2 modules Drilling diameter 67 mm For wiring accessories using screws or claws	10	0 893 72	Box ext. dim. (mm) Cover dim. (mm) 115 x 115 x 40 mm 135 x 135 mm
			10	0 893 73	160 x 105 x 40 mm 190 x 135 mm
			10	0 893 74	170 x 170 x 50 mm 195 x 195 mm
			10	0 893 75	230 x 170 x 50 mm 225 x 210 mm
		Multi-gang boxes For wiring equipment using screws Drilling diameter 67 mm Supplied with 1 removable divider for accommodating extended functions			Batibox multimedia boxes Multi-material flush-mounting boxes for connecting wall-mounted LCD or plasma screens Supplied with 2 Mosaic programme 5-module supports for flush-mounting high/low current functions (e.g.: 2P+E, TV sockets, HDMI, RCA sockets, etc.) Supplied without sockets Can be installed in advance to reserve the future space for a screen Extra-slim cover with cut-out panel for cable outlet Equipped with a site protective cover Storage space for cords Supplied with retaining bar for cords Suitable for solid or cavity walls. Depth: 50 mm
15	Depth 40 0 800 49	For 83.5 mm fixing centres Compatible with: Arteor, Mosaic and Mosaic ranges 3 modules horizontal mounting	1	0 801 93	Max. capacity: 1 x 5 modules Dimensions: 142 x 142 mm
30	0 800 42 Depth 50 0 800 52	For 71 mm fixing centres Compatible with: Arteor, Mosaic, Valena Life/Allure, Niloé, Kaptika 2-gang or 4/5 modules Horizontal or vertical use	1	0 801 95	Max. capacity: 2 x 5 modules Dimensions: 285 x 142 mm
30	0 800 43 Depth 50 0 800 53	3-gang or 6/8 modules Horizontal or vertical use			
30 15	0 800 44 Depth 50 0 800 54	4-gang or 8/10 modules Horizontal or vertical use	5	0 893 11	Box for residential environments 4-face box: - 2 faces with 7 x Ø16, 5 x Ø20 and 1 x Ø25 - 2 faces with 6 x Ø16, 3 x Ø20, 1 x Ø25 and 1 x Ø32 Dimensions: 200 x 200 x 85 mm Autoextinguibility: 850°/5 s Fixing with screws, pins or staples Closing of lid by ¼ turn Can also be used with false ceiling and raised floors
		Universal covers For converting wiring devices boxes into junction boxes or for closing up an existing box Supplied without fixing screws For one-gang or multi-gang boxes			
20	0 801 80	Round cover, Ø85 mm, for 1-gang box			Junction box depth 40 mm For 1-gang mechanisms Drilling diameter: 85 mm Supplied with square lid 100 x 100 mm
20	0 892 81	Square cover, 80 x 80 mm, for 1-gang box	10	Depth 40 0 800 84	
10	0 801 82	Cover for Batibox and Ecobatibox 2-gang box			
		Accessory Long screw Ø3 mm length 40 mm			