



| Pack | Cat.Nos | Black Colson U.V. protected cable ties | | | | |
|------|----------|---|------------------|----------------------|------|-----------------------|
| | | Designed for installation with less effort Conform to IEC 62275 type 1 | | | | |
| | | External teeth | | | | |
| | | Packaging offering several places to access the cable ties and hanging options (except Cat.No 0 319 21) | | | | |
| | | Width (mm) | Flat length (mm) | Ø grip capacity (mm) | | Tensile Strength (kg) |
| | | | | max. | min. | |
| 100 | 0 319 10 | 9 | 123 | 22 | 4 | 36 |
| 100 | 0 319 13 | 9 | 185 | 42 | 10 | 36 |
| 100 | 0 319 16 | 9 | 262 | 62 | 26 | 53 |
| 100 | 0 319 19 | 9 | 357 | 92 | 26 | 53 |
| 500 | 0 319 20 | 9 | 498 | 140 | 74 | 53 |
| 100 | 0 319 21 | 9 | 750 | 220 | 74 | 53 |
| 100 | 0 319 22 | 6 | 119 | 25 | 4 | 22 |
| 1000 | 0 319 25 | 6 | 180 | 45 | 10 | 22 |
| | | External teeth - large quantity boxes | | | | |
| | | Large quantity box with under conditioning: bag of 100 cable ties | | | | |
| 5000 | 2 008 63 | 9 | 185 | 42 | 10 | 36 |
| 2500 | 2 008 64 | 9 | 262 | 62 | 26 | 53 |
| 2000 | 2 008 65 | 9 | 357 | 92 | 26 | 53 |
| | | Internal teeth | | | | |
| | | Manual tightening | | | | |
| 100 | 0 319 28 | 7.6 | 128 | 22 | 8 | 36 |
| 100 | 0 319 29 | 7.6 | 194 | 42 | 15 | 45 |
| 100 | 0 319 30 | 7.6 | 260 | 62 | 15 | 45 |
| 100 | 0 319 32 | 7.6 | 359 | 92 | 15 | 45 |

| Pack | Cat.Nos | Black U.V. protected bases | |
|------|----------|---|--|
| 1000 | 0 319 55 | Standard plug base Ø8 mm drilling (Ø7 mm smooth material) | |
| 100 | 0 319 58 | Wall spacer plug base Ø8 mm drilling (Ø7 mm smooth material) | |
| 100 | 0 319 50 | Screw-on base, can be fixed with plug Cat.No 0 319 57 or metal stud Ø7 mm pitch 150 or countersunk screw Ø5 mm | |

| Pack | Cat.Nos | Black U.V. protected screw-in plug | |
|------|----------|---|--|
| 100 | 0 319 57 | For fixing screw-on base and cable ties with base Ø8 mm drilling (Ø7 mm smooth material) Threaded head Ø6.6 mm pitch 150 Supplied with punch for inserting pin | |
| | | Black U.V. protected cable tie with base | |
| | | Adjustable for conduits IRL Ø16 to 32 mm or for cable Ø13 to 38 mm Fixing by Ø7 mm thread 150 mm pin, screw in wall plugs Cat.No 0 319 57, screw Ø5 mm Can be fixed using Pulsa 700 E staple gun Black colour | |
| 100 | 0 319 02 | | |
| | | Colson tools | |
| | | Used for crimping and cutting off the excess strap close to the head of Colson cable ties | |
| 1 | 0 319 96 | Tool for crimping and cutting the strap in 2 separate actions | |
| | | Automatic tool | |
| 1 | 0 319 97 | Can be used to crimp Colson cable ties with one hand thanks to its automatic feedforward function After crimping, the surplus cable tie is automatically cut off without further action Simplifies installation and requires less effort Crimping tension can be adjusted with a thumbwheel at the end of the tool | |