

MULTI-OUTLET SOLUTIONS

# Plug in as you wish, anywhere!

Whether you want to recharge devices or plug in your equipment, our innovative and ingenious multi-outlet solutions will meet your needs efficiently, anywhere in your home or at work!



See p. 833

**TV multi-outlet extension**  
Cat. No 6 945 95



See p. 833

**Angled multi-outlet extension with USB ports**  
Cat. No 6 945 02



See p. 833

**Charging station with wireless charger and USB ports**  
Cat. No 6 945 00



See p. 834

**Clip-on multi-outlet extension**  
Cat. No 6 948 12

## Multifunction multi-outlet extensions



6 945 44



6 945 27



6 945 32

For indoor use only  
16 A - 230 V - 3680 W MAX

Pack	Cat.Nos	Multi-outlet extensions without cord - with switch
		Equipped with: - flush socket outlets angled 45° (except for one angled 90° for plugging in a bulky transformer without locking out another socket) - 1 On/Off illuminated switch - rotating body To be cabled with a 3G 1.5 mm <sup>2</sup> cord Can be fixed with screws (not supplied) or cable ties (not supplied)
5	6 945 43	<b>3 x 2P+E</b> ○ White/Dark Grey
5	6 945 44	<b>4 x 2P+E</b> ○ White/Dark Grey
5	6 945 45	● Black/Dark Grey
5	6 945 46	<b>5 x 2P+E</b> ○ White/Dark Grey
5	6 945 47	<b>6 x 2P+E</b> ○ White/Dark Grey
5	6 945 48	● Black/Dark Grey
		<b>Multi-outlet extensions with cord and switch</b>
		Equipped with: - flush socket outlets angled 45° (except for one angled 90° plugging in a bulky transformer without locking out another socket) - 1 On/Off illuminated switch - rotating body Can be fixed with screws (not supplied) or cable ties (not supplied)
5	6 945 27	<b>3 x 2P+E - 1.5 m cord</b> ○ White/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 28	● Black/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 35	<b>3 x 2P+E - 3 m cord</b> ○ White/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 41	<b>3 x 2P+E - 5 m cord</b> ○ White/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 29	<b>4 x 2P+E - 1.5 m cord</b> ○ White/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 30	● Black/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 36	<b>4 x 2P+E - 3 m cord</b> ○ White/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 37	● Black/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 31	<b>5 x 2P+E - 1.5 m cord</b> ○ White/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 32	● Black/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 38	<b>5 x 2P+E - 3 m cord</b> ○ White/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 42	<b>5 x 2P+E - 5 m cord</b> ○ White/Dark Grey - 3G 1.5 mm <sup>2</sup>