

## Multifunction multi-outlet extensions (continued)



For indoor use only  
16 A - 230 V - 3680 W MAX

### Pack Cat.Nos Multi-outlet extensions with cord and switch (continued)

Pack	Cat.Nos	Multi-outlet extensions with cord and switch (continued)
5	6 945 33	6 x 2P+E - 1.5 m cord
5	6 945 34	● White/Dark Grey - 3G 1.5 mm <sup>2</sup>
		● Black/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 39	6 x 2P+E - 3 m cord
5	6 945 40	● White/Dark Grey - 3G 1.5 mm <sup>2</sup>
		● Black/Dark Grey - 3G 1.5 mm <sup>2</sup>

### Multi-outlet extensions with cord and SPD

Equipped with:  
- flush socket outlets angled 45° (except for one angled 90° plugging in a bulky transformer without locking out another socket)  
- 1 On/Off illuminated switch  
- rotating body  
Can be fixed with screws (not supplied) or cable ties (not supplied)  
Integrated surge protective device (SPD): protects electronic equipment against lightning strikes  
Indicator signalling the surge protective device status:  
- green LED: the multi-outlet extension is protected  
- LED off: the multi-outlet extension is not protected but functional

5	6 945 07	4 x 2P+E - 1.5 m cord
5	6 945 11	● White/Dark Grey - 3G 1.5 mm <sup>2</sup>
		● Black/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 09	6 x 2P+E - 1.5 m cord
5	6 945 13	● White/Dark Grey - 3G 1.5 mm <sup>2</sup>
		● Black/Dark Grey - 3G 1.5 mm <sup>2</sup>

### Multi-outlet extensions with cord, MCB and overload indicator

Equipped with:  
- flush socket outlets angled 45° (except for one angled 90° plugging in a bulky transformer without locking out another socket)  
- 1 On/Off illuminated switch  
- rotating body  
Can be fixed with screws (not supplied) or cable ties (not supplied)  
Resettable overload protection (MCB) with LED indicator:  
- green LED: normal consumption  
- red LED: near maximum charge  
- LED off: power off due to an overload. To reset, unplug the device and press the reset button on the side of the multi-outlet extension

5	6 945 25	4 x 2P+E - 1.5 m cord
		● White/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 26	6 x 2P+E - 1.5 m cord
		● White/Dark Grey - 3G 1.5 mm <sup>2</sup>

### Pack Cat.Nos Multi-outlet extensions with cord, SPD and USB ports

Equipped with:  
- flush socket outlets angled 45° (except for one angled 90° plugging in a bulky transformer without locking out another socket)  
- 1 On/Off illuminated switch  
- 2 x USB Type-A and USB Type-C ports, 3.0 A - 5.0 V - 15 W MAX. Used for recharging smartphones, tablets and other electronic devices  
- rotating body  
Can be fixed with screws (not supplied) or cable ties (not supplied)  
Integrated surge protective device (SPD): protects electronic equipment against lightning strikes  
Indicator signalling the surge protective device status:  
- green LED: the multi-outlet extension is protected  
- LED off: the multi-outlet extension is not protected but functional

5	6 945 08	3 x 2P+E - 1.5 m cord
5	6 945 12	● White/Dark Grey - 3G 1.5 mm <sup>2</sup>
		● Black/Dark Grey - 3G 1.5 mm <sup>2</sup>
5	6 945 10	5 x 2P+E - 1.5 m cord
5	6 945 14	● White/Dark Grey - 3G 1.5 mm <sup>2</sup>
		● Black/Dark Grey - 3G 1.5 mm <sup>2</sup>