

Travel adaptors and TV plugs



Pack	Cat.Nos	Travel adaptors
10	Cardboard 0 503 87	With safety shutters For connecting a plug onto a different standard socket ○ White/Grey Multi-standard -> British standard adaptor 2P+E - 13 A outlet - 3250 W at 250V~ Multi-standard plug on a British standard socket Overload protection by fuse (integrated)
10	0 503 83	British standard adaptor → French standard adaptor 2P+E - 16 A outlet - 13 A input - 3.000 W at 230 V~ British standard plug on a French or German standard socket
10	0 503 82	German standard adaptor → French standard adaptor 2P+E - 16 A outlet - 3.680 W in 230 V~ German standard plug (countries: Germany, Spain, Austria, Portugal, Greece, Hungary...) on a French socket
10	0 503 85	2P adaptors - Euro/US US standard → European standard US standard plug on a French or German standard socket - 1.380 W max.
10	0 503 86	European standard → US standard French or German standard plug on a US standard socket - 1.875 W max.
50	0 500 09	TV plugs Ø9.52 mm Male plug
50	0 500 10	Female plug

Fluorescent inspection lamps

German standard



Conform to EN 61 242 A 11
3000 W - 230 V~ (cable fully unrolled) with thermal switch protection (manually resettable)

Pack	Cat.Nos	E27 inspection lamps
1	0 622 11	Steel rotary guard with protective coating Supplied with LED lamp for better impact resistance Also works with 230 V compact fluorescent and halogen lamps with an E27 base. Rubber handle Protective glass made of toughened glass IP 55 - with switch and adjustable clamp 230 V - with 2P plug - 10/16 A 10 m cable - Class II
1	0 622 10	IP 55 - without clamp 230 V - with 2P plug - 10/16 A 10 m cable - Class II
1	0 622 15	24 V - with straight Hypra plug 10 m cable - Class III
1	0 622 42	LED inspection lamp Rubber membrane gland and handle Shockproof lamp glass LED 900 lumens - IK05 IP64 in inspection lamp configuration hung up on its hook 5 m long power cord with 2P plug, red for increased visibility Withstands extreme temperatures: -20°C/+40°C