

Lighting equipment

Shaverlights



IP 44 / IK 07
 Horizontal or vertical mounting
 Screwless connection terminals
 Lifetime : 40 000 hours
 Temperature : 4000K
 Installation areas : collective housing, student housing, hotels, schools, health institutions, prisons...

Pack	Cat.Nos	Ceiling roses
10	0 601 95	Terminals: 5 x 0.75 mm ² , 3 x 1.5 mm ² , 2 x 2.5 mm ² , 2 x 4 mm ² Strong load grips support: up to 5 kg With screw connection 3 pin ceiling rose - 250 V - 6A
20	0 601 96	With plug-in connection 3-pin
20	0 601 98	4 pin white. Fire resistant UL94Vo
20	0 601 97	4 pin red. Fire resistant UL 94 Vo

Pack	Cat.Nos	Led Compact Shaverlights - 700 lm
1	SL-189800	Dimensions: 5.6 x 36 cm ON/OFF
1	SL-189801	With sensitive switch
Pack	Cat.Nos	Led Shaverlights - 800 lm
1	SL-189810	Dimensions: 6 x 50 cm Without switch
1	SL-189820	With sensitive switch
1	SL-189830	With motion sensor

Pack	Cat.Nos	E 27 lampholder
50	0 601 21	Insulating material - 100 W Screw connection Threaded base - single bushing 10 mm connector With retaining screw 4 A - 250 V~

Pack	Cat.Nos	Lampholders for public lighting
10	0 601 30	Porcelain - white Base retaining clip, protective skirt 4 A - 250 V~ E 27 lampholder
10	0 601 80	Base retaining clip - 16 A max. One piece unit 16 A - 500 V~ E 40 lampholder

Pack	Cat.Nos	Cord switches
20	0 401 87	Fluorescent Easy connection by cutting the 2 wires Double pole White spotted
20	0 401 92	Coloured Easy connection by cutting the 2 wires Double pole White
20	0 401 93	Old gold, old gold rocker
20	0 401 94	Black

Pack	Cat.Nos	Door contact switch
10	0 401 75	Normally closed contactor complete with roller actuator Automatically illuminates cupboards upon opening of the door Single pole 2 A - 250 V