






IP 44/54/55 weatherproof bulkhead lights



Dimensions p. 902

Pack	Cat.Nos	IP 55 - IK 10 LED round decorative bulkhead lights - equipped	IP 44/54 - IK 04 bulkhead lights to be equipped
1	SL-532106	4000 K – IRC 80 Life time: 40,000 hours Screwless connection terminals	Chartres Origine - IP 54 round decorative bulkhead light  E 27 bulkhead light for exterior use Ø340 mm Polycarbonate base Self-extinguishing: 850 °C 30 sec. Compact fluorescent lamp (max. 20 W) can be used in bulkhead lights with E 27 lampholder High resistance weatherproof seal Captive screws Automatic terminals 75 W bulkhead light Electrical connection: 1 entry via the rear with membrane gland Supplied without lamp in cardboard box
1	SL-532146	Chartres Essentiel bulkhead lights Ø300 mm - 1500 lm Polycarbonate base and diffuser with captive screws ON/OFF With microwave sensor	
1	SL-532180	IP 44 - IK 07/09 LED round decorative bulkhead lights - equipped Ø330 mm 4000 K – IRC 80 Life time: 40,000 hours Polycarbonate base and opal diffuser with captive screws Screwless connection terminals	Super 400 - IP 44 round bulkhead lights With integrated HF sensor - E 27 Ø296 mm Polypropylene base Transparent tempered glass diffuser assembled via a 1/4 turn rotation Compact fluorescent lamps can be used in bulkhead lights (max. 20 W) with E 27 lamp-holder ON/OFF - E 27 Consumption: 70 W / 23 W max. Supplied without lamp Allows automatic ON/OFF switching Pre-configured settings: - time delay: 5 seconds to 25 minutes - range: 1 to 8 m - light level threshold: 0 to 30 lux Consumption: 53 W / 20 W max. Supplied without lamp
1	SL-532185	Astreo IK 07 bulkhead lights  800 lm - ON/OFF 800 lm - with microwave sensor 1400 lm - ON/OFF 1400 lm - with microwave sensor	
1	SL-532182		SL-524270  1
1	SL-532187		
1	SL-532190	Astreo IK 09 vandal-resistant bulkhead lights  800 lm - ON/OFF 800 lm - with microwave sensor	SL-500270  1
1	SL-532195		