

Linkeo 19" freestanding cabinets

cabinets and equipment (continued)



6 465 06



6 465 01



6 465 20

Pack Cat.Nos Linkeo fixed shelves

		Black RAL 9005 Screw fixing	
		Projecting mounting on 2 x 19" uprights	
1	6 465 01	Height 2U. Max. load: 15 kg	
1	6 465 02	Shelf depth 200 mm	
		Shelf depth 360 mm	
		Mounting on 4 x 19" uprights	
		Height 1U	
1	6 465 05	Max. load: 50 kg	
		Shelf depth 425 mm	
1	6 465 06	For depth 600 mm	
		Shelf depth 625 mm	
1	6 465 07	For depth 800 mm	
		Shelf depth 825 mm	
		For depth 1000 mm	

Linkeo telescopic shelves

		Screw fixing on 4 x 19" uprights. Height 1U	
		Max. load: 30 kg. Black RAL 9005	
1	6 465 08	Shelf depth 425 mm	
		For depth 600 mm	
1	6 465 09	Shelf depth 625 mm	
		For depth 800 mm	
1	6 465 10	Shelf depth 825 mm	
		For depth 1000 mm	

19" management panels

		Fitted with cable guide rings	
1	6 465 20	1U	
1	6 465 21	2U	

LED Lighting

		Prewired with 2 m length power cord	
		Magnets fastening	
1	0 464 91	With switch	
		60° swivel	
1	0 363 81	With presence sensor	
		120° swivel	

Linkeo 19" freestanding cabinets

Flatpack solution

Easy to carry
Easy to store
Easy to handle
Easy to assemble
- 16 minutes/1 person
- dedicated installation sheet

High-protection packaging (stackable)

Note:

- Flatpacked cabinets are exactly the same as ready-assembled ones. The only difference is the packaging.



Made-to-measure solutions

1 Choose the size

Capacity	24U	33U	42U	47U
Width	600 or 800 mm			
Depth	600, 800 or 1000 mm			

2 Choose the colour

3 Choose the openings



Front and rear options

Doors in single- or double-door versions

- screen-printed glass, microperforated metal, solid metal, etc.⁽¹⁾

¹: To discover the full range of possibilities, please contact your Legrand representative.

With or without side panels

4 Choose the equipment to be factory-mounted

- cable managers
- fans
- plinths
- shelves
- fibre and copper patch panels