

# Linkeo 19" and 10" wall-mounting cabinets



6 462 62



6 462 21



6 462 30



0 337 98

0 462 23



6 468 01

IP 20 - IK 08

Equipped with:

- reversible flat screen-printed safety glass door with integrated lock
- 2 x 19" uprights, with U marking and adjustable in depth
- 3 pre-cut cable entries (top, bottom and rear)

- 1 brush seal for cable entry
  - top perforations for natural ventilation
- Anthracite grey RAL 7016

Pack	Cat.Nos		Linkeo 19" fixed cabinets			
			<b>Fixed side panels</b>			
			Delivered ready-assembled Side panels with automatic earthing			
	Depth 450 mm	Depth 600 mm	Capacity	Height (mm)	Width (mm)	Loading capacity (kg)
1	6 462 00	6 462 10	6U	359	600	18
1	6 462 01	6 462 11	9U	492	600	27
1	6 462 02	6 462 12	12U	625	600	36
1	6 462 03	6 462 13	15U	759	600	45
1	6 462 04	6 462 14	18U	892	600	54
1	6 462 05	6 462 15	21U	1025	600	63
			<b>Removable side panels</b>			
			For easy access at the side of the cabinet Opening with a lock (same key as the door). Delivered flat-packed. Supplied with earthing kit			
1	6 462 50	6 462 60	6U	359	600	18
1	6 462 51	6 462 61	9U	492	600	27
1	6 462 52	6 462 62	12U	625	600	36
1	6 462 53	6 462 63	15U	759	600	45
1	6 462 54	6 462 64	18U	892	600	54
1	6 462 55	6 462 65	21U	1025	600	63

Pack	Cat.Nos		Linkeo 19" pivoting cabinets			
			Consisting of:			
			- plinth (wall fixing), able to take a 19" PDU			
			- pivoting body allowing free access to the rear of the cabinet to facilitate installation and maintenance. Reversible pivoting direction. Delivered ready-assembled			
			Side panels with automatic earthing			
	Depth 610 mm		Capacity	Height (mm)	Width (mm)	Loading capacity (kg)
1	6 462 21		9U	492	600	27
1	6 462 22		12U	625	600	36
1	6 462 23		15U	759	600	45
1	6 462 24		18U	892	600	54
1	6 462 25		21U	1025	600	63

Pack	Cat.Nos		Equipment for 19" cabinets			
			<b>Linkeo 19" uprights</b>			
			Set of 2 additional 19" uprights For installation at the back of the cabinet			
1	6 462 42		12U			
1	6 462 43		15U			
1	6 462 44		18U			
1	6 462 45		21U			
1	6 462 48		<b>Casters</b> Set of 4 casters for pivoting cabinet			
1	6 462 38		<b>Linkeo fan kit</b> Kit contains: - 2 fans - 1 thermostat - switch Supplied with 2.3 m cable 230 V~ - 50/60 Hz power supply			

Pack	Cat.Nos		Equipment for 19" cabinets (continued)			
			<b>Linkeo fixed shelves</b>			
			Screw fixing (projecting) on 2 x 19" uprights Height 2U Max. load: 15 kg Black RAL 9005			
1	6 465 01		Shelf depth 200 mm For cabinets depth 400, 450 and 600 mm			
1	6 465 02		Shelf depth 360 mm For cabinets depth 450 and 600 mm			
			<b>19" management panels</b>			
			Fitted with cable guide rings			
1	6 465 20		1U			
1	6 465 21		2U			
			<b>Linkeo 10" cabinets</b>			
			Compact cabinet, suitable for small business applications Delivered ready-assembled Side panels with automatic earthing			
1	Depth 300 mm	6 462 30	Capacity	Height (mm)	Width (mm)	Service load (kg):
			6U	359	370	18

Pack	Cat.Nos		Equipment for 10" cabinets			
			<b>Flat patch panel with 6 connectors - 1U to be equipped</b>			
			Takes up to 6 cat. 5e to cat. 8 RJ 45 connectors 10" panel - 1U			
1	0 337 98					
			<b>Flat patch panel with 12 connectors - 1U to be equipped</b>			
			Takes up to 12 cat. 5e to cat. 6 <sub>A</sub> RJ 45 connectors 10" panel - 1U			
1	0 337 99					
			<b>Fixed shelf 1U</b>			
			Depth 120 mm Max. load: 10 kg Black RAL 9005 Supplied with screws and cage nuts			
1	0 462 23					
			<b>Fan</b>			
			2.5 m power supply cable 230 V~ fan			
1	0 462 60					
			<b>Thermostat</b>			
			Adjustable from 5 to 60°C, 230 V~, 50/60 Hz NC contact (5 A) and NO contact (10 A) Magnetic mounting			
1	0 348 48					
			<b>10" PDUs (Power Distribution Units)</b>			
			230 V~ - 50/60 Hz power supply Aluminium case height 1U End caps with metal brackets Integrated cable guide Quick fixing (no screws) on 19" upright			
1	6 468 01		Block of 4 x 2P+E outlets, black, at a 55° angle with safety shutter, German standard 1 m power supply cord with 16 A 2P+E French/German plug			
1	6 468 00		Block of 4 x 2P+E sockets, black, at a 55° angle with safety shutter, French standard 1 m power supply cord with 16 A 2P+E French/German plug To be equipped			
1	6 468 98		Capacity: 8 Mosaic modules			

For overall cabinet dimensions, see p. 950-951