

## Linkeo 19" vertical cabinet



6 462 40

IP20 - IK 08

Compact cabinet, suitable for small business applications or floor distributors

Equipment mounted vertically

Delivered ready-assembled

Equipped with:

- Flat metal door with integrated lock
- 2 x 19" uprights, 3U at the front and 1U at the rear (for mounting the PDU)
- 1 brush seal for top cable entry
- top perforations for natural ventilation

Supplied with earthing kit

Anthracite grey RAL 7016

Pack	Cat.Nos	Linkeo 19" vertical cabinet			
1	6 462 40	Compact cabinet, suitable for small business applications Delivered ready-assembled	Capacity 3U + 1U	Height (mm) 569	Width (mm) 538

### Thermal management

1	0 462 60	<b>Fan</b> 2.5 m power supply cable 230 V~ fan
1	0 348 48	<b>Thermostat</b> Adjustable from 5 to 60°C, 230 V~, 50/60 Hz NC contact (5 A) and NO contact (10 A) Magnetic mounting

## 19" Bati-rack



0 463 96 + 2 x 0 463 97



0 463 97



6 465 01





6 465 20



Technical characteristics p. 951

Pack	Cat.No.s	19" Bati-rack						
		For housing 19" equipment in an air-conditioned, secure, dust-free environment Comprises 2 or 4 x 19" uprights With levelling feet The 4-upright bati-rack takes shelves and fixed runners for cabinets depth 800 mm Delivered flatpacked RAL 7035						
1	0 463 95	Capacity	Height <sup>(1)</sup> (mm)	Width (mm)	Depth (mm)	Loading capacity (kg)	Number of uprights	
1	0 463 96	42U	1965	550	640	300	2	
		42U	1965	550	820	300	4	
1	0 463 97	<b>Cable management sleeve</b> Closed vertical feedthrough Reversible door For fixing on the right or left of 19" uprights RAL 7035						
1	0 464 98	<b>Roof</b> Roof for 4-upright bati-rack 535 x 600 mm						
1	0 464 99	<b>Set of 4 casters</b> For bati-rack Loading capacity on the 4 casters: 340 kg						
1	6 465 01	<b>Shelves</b> Black RAL 9005 <b>Screw fixing (projecting) on 2 x 19" uprights</b> Height 2U Max. load: 15 kg						
1	6 465 02	Shelf depth 200 mm Shelf depth 360 mm						
1	6 465 06	<b>Screw fixing on 4 x 19" uprights</b> Height 1U Shelf depth 625 mm. Max. load: 50 kg						
1	6 465 09	Telescopic shelf depth 625 mm. Max. load: 30 kg						
1	6 465 20	<b>19" management panels</b> Fitted with cable guide rings 1U						
1	6 465 21	2U						





1: Height without levelling feet (+27 to 42 mm with feet)