

Altis™ 19" freestanding cabinets IP 55 - IK 10



0 473 62 + 0 472 72
+ 0 482 20

0 473 63 equipped

Cable ties and document holders



0 331 94

0 331 95

0 331 85

0 331 85

0 331 87

0 320 68

Pack Cat.Nos Altis 19" 42 U cabinets

Cabinets with framed glass door

Protection against dust, water, knocks in demanding environments - IP55 - IK10
For loads up to 720 kg on four 19" uprights
Reversible door with toughened glass window
4-point locking with double bar (key barrels Cat.No 0 347 89)
Removable rear panel
Cable entries at bottom (plates Cat.Nos 0 481 52/54/68/69/78/79)
Can be equipped with plinth (Cat.Nos 0 476 56/57/66/67/73/74/78/79/88/89)
19" uprights and side panels to be ordered separately
Grey RAL 7035

Pack	Cat.Nos	Dimensions			Window dim.		Weight (kg)
		Height (mm)	Width (mm)	Depth (mm)	Height (mm)	Width (mm)	
1	0 473 62	2000	600	600	1775	375	91.7
1	0 473 63	2000	800	600	1775	575	110.4
1	0 473 91	2000	600	800	1775	375	95.2
1	0 473 92	2000	800	800	1775	575	114.6

Set of 2 side panels

For cabinets	
Height (mm)	Depth (mm)
2000	600
2000	800

19" uprights
Set of 2 42 U uprights (perforations 9.5 x 9.5 mm)
Supplied with mounting lugs and screws
Mounting in cabinets possible width 600 or 800 mm


Interior assembly kit - IP 55 for a 1000 kg/m³ load
Set consisting of
- 4 brackets
- 2 joining feet
- 1 gasket

M 14 lifting rings
Set of 4 rings
For a load of 1000 kg/m³

For grouping together and organising audio, computer, VDI, etc., cables
Re-usable (cables can be added)

Pack Cat.Nos Cable ties with tightening indicator

Wide cable ties with patented warning system to prevent overtightening cables
Release by pinching the head of the cable tie
Strap held in place after tightening



Pack	Cat.Nos	Width (mm)	Length (mm)	Tightening Ø	
				max.	min.
50	0 331 94	15	180	35	15
50	0 331 95	15	225	50	35
50	0 331 96	15	320	80	50

Self-locking cable ties

Repositionable cable ties
Double-sided textile with "loops" on one side and "hooks" on the other
Do not damage cables
Can be fixed using screws or rivets
Cat.Nos 0 366 44/46 (p. 425)

Pack	Cat.Nos	Colour	Width (mm)	Length (mm)	Tightening Ø
					max. (mm)
10	0 331 84	Black	16	150	35
10	0 331 85	Red	16	150	35
10	0 331 86	Green	16	150	35
10	0 331 87	Black	16	300	80
10	0 331 88	Red	16	300	80
10	0 331 89	Green	16	300	80

Self adhesive base


50 0 320 68 For cable ties max. width 20 mm
Black - 38 x 38 x 9.4 mm
Possible central fixing with screw Ø4 mm



Self-adhesive document holders

Open - RAL 7035

Pack	Cat.Nos	Ext. dimensions		Int. dimensions		
		Height (mm)	Width (mm)	Height (mm)	Width (mm)	Depth (mm)
20	0 365 80	235	340	200	310	18
20	0 365 81	165	260	130	230	18



Closed - RAL 7035

1 0 365 82 Rigid plastic - IP 50
Int. dimensions: 324 x 120 x 18 mm

Transparent

10 0 097 99 Soft plastic, A4 - 305 x 220 mm