

Legrand cabling system, LCS³ cat. 6_A

RJ 45 sockets - Mosaic™



Can be integrated in any support
Mechanisms to be equipped with support frames and plates
Equipped with connectors with quick toolless connection
Take single-core cables from AWG 22 up to AWG 26, and AWG 26 multicore cables
T568A and B marking with colour codes
Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards

Pack	Cat.Nos	Cat. 6 _A RJ 45 sockets - Mosaic
10	0 765 73	STP - 1 module Metal shielding ○ White
10	0 765 84	○ White antimicrobial ⁽¹⁾
10	0 794 73	● Aluminium
10	0 791 73L	● Matt Black
10	0 765 76	STP - 2 modules Metal shielding ○ White
10	0 794 76	● Aluminium
10	0 791 76L	● Matt Black
10	0 765 24	○ White with green shutter
10	0 765 25	○ White with orange shutter
5	0 765 99	STP with controlled access - 2 modules Metal shielding Supplied with 2 keys for 5 sockets ○ White with red shutter
10	0 765 08	STP 45° - 2 modules Metal shielding ○ White
10	0 765 71	UTP - 1 module ○ White
10	0 794 71	● Aluminium
10	0 765 26	○ White with green shutter
10	0 765 27	○ White with orange shutter
10	0 765 74	UTP - 2 modules ○ White
10	0 794 74	● Aluminium
5	0 765 90	UTP with controlled access - 2 modules Supplied with 2 keys for 5 sockets ○ White with red shutter
10	0 765 09	UTP 45° - 2 modules ○ White

1: Contains a silver compound which prevents the growth of bacteria on the surface

Legrand cabling system, LCS³ cat. 6_A

RJ 45 sockets - Arteor



Can be integrated in any support
Mechanisms to be equipped with support frames and plates
Equipped with connectors with quick toolless connection
Take single-core cables from AWG 22 up to AWG 26, and AWG 26 multicore cables
T568A and B marking with colour codes
Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards

Pack	Cat.Nos	Cat. 6 _A RJ 45 sockets - Arteor
10	5 723 06	Metal shielding
10	5 728 06	STP - 1 module ○ White
10	5 728 46	● Magnesium
10	5 728 45	● Champagne
10	5 728 45	● Soft Alu
10	5 723 51	○ White with orange shutter
10	5 728 51	● Magnesium with orange shutter
10	5 728 48	● Champagne with orange shutter
10	5 728 47	● Soft Alu with orange shutter
10	5 723 52	○ White with green shutter
10	5 728 52	● Magnesium with green shutter
10	5 728 61	● Champagne with green shutter
10	5 728 60	● Soft Alu with green shutter
5	5 723 50	STP with controlled access - 2 modules Supplied with 2 keys for 5 sockets ○ White with red shutter
5	5 728 50	● Magnesium with red shutter
5	5 728 63	● Champagne with red shutter
5	5 728 62	● Soft Alu with red shutter
10	5 723 49	UTP - 1 module ○ White
10	5 728 49	● Magnesium
10	5 728 65	● Champagne
10	5 728 64	● Soft Alu
10	5 723 58	○ White with orange shutter
10	5 728 58	● Magnesium with orange shutter
10	5 728 69	● Champagne with orange shutter
10	5 728 68	● Soft Alu with orange shutter
10	5 723 59	○ White with green shutter
10	5 728 59	● Magnesium with green shutter
10	5 728 67	● Champagne with green shutter
10	5 728 66	● Soft Alu with green shutter
5	5 723 57	UTP with controlled access - 2 modules Supplied with 2 keys for 5 sockets ○ White with red shutter
5	5 728 57	● Magnesium with red shutter
5	5 728 72	● Champagne with red shutter
5	5 728 71	● Soft Alu with red shutter