

## Legrand cabling system, LCS<sup>3</sup> cat. 6<sub>A</sub>

other RJ 45 connectors



6 327 79



0 337 49



0 695 59L

Pack	Cat.Nos	Cat. 6 <sub>A</sub> Keystone RJ 45 sockets
10	0 331 54	STP socket - metal shielding with quick toolless connection
10	0 331 55	UTP connector - with quick toolless connection
1	6 327 79	<b>Surface-mounting box - 1 or 2 ports</b> For Keystone connectors For surface-mounting installations Can be fixed to a table or used in conjunction with mini-trunking
1	0 337 43	<b>STP cat. 6<sub>A</sub> cable extender</b> To be used to extend a cable quickly and easily
1	0 337 49	<b>STP cat. 6<sub>A</sub> field plug</b> To be used to make a direct connection on any IP equipment (switch, PoE LED panel, camera, Wi-Fi access point, etc) No tools required
5	0 695 59L	<b>STP cat. 6<sub>A</sub> Plexo RJ 45 socket</b> IP 55 closed flap IK 08 ● Grey



## Legrand cabling system, LCS<sup>3</sup> cat. 6<sub>A</sub>

zone distribution box solution



0 337 97



0 337 75



0 786 28

Pack	Cat.Nos	Zone distribution boxes to be equipped
1	0 337 96	For distributing data in an area equipped with 1 to 24 RJ 45 sockets Centralise connections to ensure flexibility and scalability of the installation For installation in false ceilings or raised access floors The boxes connect to the patching enclosure or floor cabinet Connection to an RJ 45 socket with an RJ 45/ stripped cord or to a Mosaic RJ 45 socket with copper feedthrough with an RJ 45/RJ 45 cord IP 21 - IK 07 Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards T568A and B marking with colour codes Technical characteristics: polycarbonate cover (PC), polypropylene base (PP), RAL 7035 To be equipped directly with High Density RJ 45 connectors
1	0 337 97	12 ports to be equipped 24 ports to be equipped
6	0 337 73	<b>Cat. 6<sub>A</sub> High Density RJ 45 connectors</b> Set of 6 RJ 45 connectors UTP
6	0 337 75	STP
1	0 517 86	<b>Cat. 6<sub>A</sub> cords - RJ 45/stripped</b> RJ 45/stripped - straight Plug in and out of the zone distribution boxes and connect to an LCS <sup>3</sup> connector of an RJ 45 socket via the stripped side Cables prepared in factory, "ready for wiring" Compliant with ISO/IEC 11801 Ed. 2.0 (2011), EN 50173-1 and EIA/TIA 568 C2 standards
1	0 517 87	<b>Shielded S/FTP, impedance 100 Ω</b> Length 8 m
1	0 517 88	Length 15 m
1	0 517 88	Length 20 m
1	0 515 23	<b>Cat. 6<sub>A</sub> cords - RJ 45/RJ 45</b> For direct connection via RJ 45 male plug to the zone distribution box and to the RJ 45 socket with copper feedthrough to ensure safe connection, plus speed and reliability of connection Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards
1	0 515 24	<b>Shielded S/FTP, impedance 100 Ω</b> Length 8 m
1	0 515 25	Length 15 m
1	0 515 25	Length 20 m
10	0 786 28	<b>Cat. 6<sub>A</sub> sockets with copper feedthrough</b> <b>Cat. 6<sub>A</sub> STP - Mosaic</b> ○ White
10	0 786 29	● Aluminium

LSZH



RAL 1018

0 517 86

0 517 87

0 517 88

LSZH



RAL 1018

0 515 23

0 515 24

0 515 25

