

Legrand cabling system, LCS³ cat. 6

RJ 45 sockets (Arteor, Soliroc and Plexo) and other connectors



Can be integrated in any support
 Equipped with connectors with quick toolless connection
 Take single-core cables from AWG 22 up to AWG 26, and AWG 26 multicore cables
 T568A and B marking with colour codes
 Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards

Pack	Cat.Nos	Cat. 6 RJ 45 sockets - Arteor
		Mechanisms supplied with square rocker plates, to be equipped with support frames and plates
		UTP - 1 module
10	5 723 02	○ White
10	5 728 02	● Magnesium
10	5 700 57	● Champagne
10	5 710 57	● Soft Alu
10	5 723 54	○ White with orange shutter
10	5 728 54	● Magnesium with orange shutter
10	5 728 74	● Champagne with orange shutter
10	5 728 73	● Soft Alu with orange shutter
10	5 723 55	○ White with green shutter
10	5 728 55	● Magnesium with green shutter
10	5 728 80	● Champagne with green shutter
10	5 728 79	● Soft Alu with green shutter
		UTP - 2 modules
10	5 723 14	○ White - square version
10	5 728 14	● Magnesium - square version
10	5 700 59	● Champagne - square version
10	5 710 59	● Soft Alu - square version
		UTP with controlled access - 2 modules Supplied with 2 keys for 5 sockets
5	5 723 53	○ White with red shutter
5	5 728 53	● Magnesium with red shutter
5	5 728 87	● Champagne with red shutter
5	5 728 86	● Soft Alu with red shutter
		UTP with retractable cord - 4 modules With integrated retractable cord (0.9 m) Automatically winds back in at the press of a button
1	5 723 39	○ White
1	5 728 39	● Magnesium
1	5 728 89	● Champagne
1	5 728 88	● Soft Alu
		FTP - 1 module
10	5 723 22	○ White
10	5 728 22	● Magnesium
10	5 728 91	● Champagne
10	5 728 90	● Soft Alu
		FTP - 2 modules
10	5 723 16	○ White
10	5 728 16	● Magnesium
10	5 728 93	● Champagne
10	5 728 92	● Soft Alu
		Shielded STP - 1 module
10	5 723 23	○ White
10	5 728 23	● Magnesium
10	5 728 95	● Champagne
10	5 728 94	● Soft Alu
		Shielded STP - 2 modules
10	5 723 17	○ White
10	5 728 17	● Magnesium
10	5 728 97	● Champagne
10	5 728 96	● Soft Alu

Pack	Cat.Nos	Cat. 6 Soliroc RJ 45 socket - IK 10
1	0 778 91	FTP - 2 modules IP 20 - IK 10 For at-risk areas or areas without surveillance
		Cat. 6 Plexo RJ 45 sockets - IP 55 closed flap IK 08
		RJ 45 sockets Protection against water, dust For industrial sites
1	0 695 61L	● Grey UTP socket
5	0 695 69L	FTP socket
		Cat. 6 Plexo 66 RJ 45 socket - IP 66 - IK 08
1	0 904 67	FTP socket 9 contacts Guaranteed weatherproof seal (IP 66) with the plug inserted Inclined 90° ● Grey RAL 7016/T029
		Cat. 6 Keystone RJ 45 socket
10	0 331 81	UTP socket with fast connection
		Surface-mounting box - 1 or 2 ports
1	6 327 79	For Keystone connectors For surface-mounting installations Can be fixed to a table or used in conjunction with mini-trunking
		Cable extenders
1	0 337 48	To be used to extend a cable quickly and easily For FTP cat. 6 cables
1	0 337 42	For UTP cat. 6 cables

Audio/video sockets
 Arteor and Mosaic
 p. 1006-1007

