

# Legrand cabling system, LCS<sup>3</sup> cat. 5e

## zone distribution box solution



0 337 97



0 337 53



0 786 25

Pack	Cat.Nos	Zone distribution boxes to be equipped
1	0 337 96	For distributing data in an area equipped with 1 to 24 RJ 45 sockets Centralise connections to ensure flexibility and scalability of the installation For installation in false ceilings or raised access floors The boxes connect to the patching enclosure or floor cabinet Connection to an RJ 45 socket with an RJ 45/stripped cord or to a Mosaic RJ 45 socket with copper feedthrough with an RJ 45/RJ 45 cord IP 21 - IK 07 Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards T568A and B marking with colour codes Technical characteristics: polycarbonate cover (PC), polypropylene base (PP), RAL 7035 To be equipped directly with RJ 45 High Density connectors
1	0 337 97	12 ports to be equipped 24 ports to be equipped

Pack	Cat.Nos	Cat. 5e High Density RJ 45 connectors
6	0 337 53	Set of 6 RJ 45 connectors UTP
6	0 337 54	FTP

Pack	Cat.Nos	Cat. 5e cords - RJ 45/RJ 45
1	0 515 03	For direct connection via RJ 45 male plug to the zone distribution box and to the RJ 45 socket with copper feedthrough to ensure safe connection, plus speed and reliability of connection <b>Screened F/UTP, impedance 100 Ω</b> Length 8 m
1	0 515 04	Length 15 m
1	0 515 05	Length 20 m
1	0 515 00	<b>Unscreened U/UTP, impedance 100 Ω</b> Length 8 m
1	0 515 01	Length 15 m
1	0 515 02	Length 20 m

Pack	Cat.Nos	Cat. 5e sockets with copper feedthrough
10	0 786 20	<b>Cat. 5e UTP - Mosaic</b> ○ White
10	0 786 24	● Aluminium
10	0 786 21	<b>Cat. 5e FTP - Mosaic</b> ○ White
10	0 786 25	● Aluminium
10	5 723 30	<b>Cat. 5e UTP - Arteor</b> ○ White
10	5 728 30	● Magnesium
10	5 729 18	● Champagne
10	5 729 17	● Soft Alu
10	5 723 32	<b>Cat. 5e FTP - Arteor</b> ○ White
10	5 728 32	● Magnesium
10	5 729 20	● Champagne
10	5 729 19	● Soft Alu