


Legrand cabling system, LCS³ fiber optic

cables



Selection chart p. 966-967

Colour code: FOTAG
 Compliant with EN 50173-2 and ISO IEC 11801 standards
 Packed on a 2000 m reel except for tight-buffer OM4
 Tight-buffer: "easy strip"
 Other configurations on request

Pack	Cat.Nos		Single-mode OS2 fiber optic cables (9/125 µm) - (OS1 compatible) For 9/125 µm single-mode installations, OS2 type Indoor/Outdoor Yellow LSZH sheath Glass strands 4 fibers - Euroclass Dca 6 fibers - Euroclass Dca 8 fibers - Euroclass Dca 12 fibers - Euroclass Dca 12 fibers - Euroclass Cca 24 fibers - Euroclass Dca 24 fibers - Euroclass Cca Outdoor Black PE sheath Glass strands for rodent-proofing, reinforced with corrugated steel 4 fibers 6 fibers 8 fibers 12 fibers 24 fibers
	Loose tube	Tight-buffer 900 µm	
2000 ¹	0 325 02	0 325 50	
2000 ¹	0 325 12		
2000 ¹	0 325 03		
2000 ¹	0 325 14		
2000 ¹	0 325 26		
2000 ¹	0 325 51		
1000 ¹	0 325 18		
2000 ¹	0 325 23		
2000 ¹	0 325 13		
2000 ¹	0 325 24		
2000 ¹	0 325 15		
2000 ¹	0 325 25		

Pack	Cat.Nos		Multimode OM3 fiber optic cables (50/125 µm) For 50/125 µm multimode installations, OM3 type Suitable for 10 Gb Ethernet networks Bend insensitive Indoor/Outdoor Aqua LSZH sheath Glass strands Euroclass Dca 4 fibers 6 fibers 8 fibers 12 fibers 24 fibers Outdoor Black PE sheath Glass strands for rodent-proofing, reinforced with corrugated steel 8 fibers 12 fibers 24 fibers
	Loose tube	Tight-buffer 900 µm	
2000 ¹	0 325 37	0 325 10	
2000 ¹			
2000 ¹			
2000 ¹			
2000 ¹			
2000 ¹			
2000 ¹	0 325 40	0 325 52	
2000 ¹	0 325 41		
2000 ¹	0 325 42		

1: in metre(s)

Pack	Cat.Nos		Multimode OM4 fiber optic cables (50/125 µm) For 50/125 µm multimode installations, OM4 type Suitable for 10 Gb Ethernet networks Bend insensitive Indoor/Outdoor Aqua LSZH sheath Glass strands 4 fibers - Euroclass Dca 6 fibers - Euroclass Dca - 500 m drum 6 fibers - Euroclass Dca - 1000 m drum 8 fibers - Euroclass Dca 12 fibers - Euroclass Dca 12 fibers - Euroclass Cca 12 fibers - Euroclass Dca - 1000 m drum 24 fibers - Euroclass Dca - 1000 m drum 24 fibers - Euroclass Cca - 1000 m drum Outdoor Black PE sheath Glass strands for rodent-proofing, reinforced with corrugated steel 4 fibers 8 fibers 12 fibers
	Loose tube	Tight-buffer 900 µm	
2000 ¹	0 325 43	0 326 65	
500 ¹			
1000 ¹		0 326 66	
2000 ¹			
2000 ¹		0 326 67	
2000 ¹			
2000 ¹			
2000 ¹			
1000 ¹	0 326 68		
1000 ¹			
1000 ¹	0 325 19		
2000 ¹	0 325 46		
2000 ¹	0 325 47		
2000 ¹	0 325 48		