

Legrand cabling system, LCS³ fiber optic

preterminated links



1 320 21

OM4 and OM5
on request



1 320 41

OM4 and OM5
on request

Selection chart p. 970-971

Supplied with pulling element. In coil up to 50 m, on a small drum between 51 m and 150 m, on a large drum over 151 m and up to 200 m

Connection in fiber optic drawers

OM3 aqua LSZH sheaths

Supplied with test reports

Possible to obtain customised preterminated links: cable type, structure, length, connector type, etc

Pack Cat.Nos Core SC/SC tight-buffer OM3 links

6 SC simplex - 6 SC simplex

Pack	Cat.Nos	Length
1	1 320 03	30 m
1	1 320 04	40 m
1	1 320 05	50 m
1	1 320 06	60 m
1	1 320 07	70 m
1	1 320 08	80 m
1	1 320 09	90 m
1	1 320 10	100 m
1	1 320 12	120 m
1	1 320 14	140 m
1	1 320 16	160 m
1	1 320 20	200 m

12 SC simplex - 12 SC simplex

Pack	Cat.Nos	Length
1	1 320 21	10 m
1	1 320 22	20 m
1	1 320 23	30 m
1	1 320 24	40 m
1	1 320 27	70 m
1	1 320 28	80 m
1	1 320 29	90 m
1	1 320 30	100 m
1	1 320 32	120 m
1	1 320 34	140 m
1	1 320 36	160 m

Pack Cat.Nos Core LC/LC tight-buffer OM3 links

6 LC simplex - 6 LC simplex

Pack	Cat.Nos	Length
1	1 320 41	10 m
1	1 320 42	20 m
1	1 320 43	30 m
1	1 320 45	50 m
1	1 320 46	60 m
1	1 320 47	70 m
1	1 320 48	80 m
1	1 320 49	90 m
1	1 320 50	100 m
1	1 320 52	120 m
1	1 320 54	140 m
1	1 320 56	160 m
1	1 320 58	180 m
1	1 320 60	200 m

12 LC simplex - 12 LC simplex

Pack	Cat.Nos	Length
1	1 320 61	10 m
1	1 320 62	20 m
1	1 320 63	30 m
1	1 320 65	50 m
1	1 320 66	60 m
1	1 320 67	70 m
1	1 320 70	100 m
1	1 320 74	140 m
1	1 320 78	180 m
1	1 320 80	200 m