

# Legrand cabling system LCS<sup>3</sup> enclosures

## server cabinets

## cabling cabinets



4 464 07



4 464 17



4 464 34

Colour: Black RAL 9005  
 Frame: aluminium, demountable  
 Load capacity: 1500 kg (static)  
 80 % perforated front door and 80 % perforated double rear doors: all doors are fitted with a Fix-easy swivel handle with a EK333 locking  
 Roof : 2 cut-outs (filled with blind plates and brushes)  
 Interior: cabinet equipped with 4 x 19" profiles including height (U) indication  
 Distance to the cabinet with airflow front: set to 80 mm (pitch set to 100 mm)  
 Distance to the cabinet front: set to 175 mm (pitch set to 100 mm)  
 Server cabinets supplied without side panels  
 Flatpack server cabinets supplied with side panels  
 Server cabinets with airflow management are supplied with an airflow management package keeping the loss of air to a minimum, thus improving energy efficiency  
 Cabinets equipped with leveling feet  
 Server cabinets with airflow management are supplied with a sideskirt with cut-outs and blind panels

Colour: Black RAL 9005  
 Frame: aluminium, demountable  
 Load capacity: 1500 kg (static)  
 Glass front door and blind steel door in the back: all doors are fitted with a Fix-easy swivel handle with a EK333 locking  
 Roof: 3 cut-outs (the left and right ones have blind plates and brushes, the center one has a blind plate)  
 Interior: cabinet equipped with 4 x 19" profiles including height (U) indication  
 Distance to the cabinet front: set to 175 mm (pitch set to 100 mm)  
 Cabinets delivered with side panels  
 Cabinets equipped with leveling feet

### LCS<sup>3</sup> 19" server cabinets

Pack	Cat.Nos	Capacity	Width (mm)	Depth (mm)
1	4 464 00	42 U	600	1000
1	4 464 01	42 U	600	1200
1	4 464 02	42 U	800	1000
1	4 464 03	42 U	800	1200
1	4 464 04	47 U	600	1000
1	4 464 05	47 U	600	1200
1	4 464 06	47 U	800	1000
1	4 464 07	47 U	800	1200

### LCS<sup>3</sup> 19" server cabinets with air flow management

Pack	Cat.Nos	Capacity	Width (mm)	Depth (mm)
1	4 464 10	42 U	600	1000
1	4 464 11	42 U	600	1200
1	4 464 12	42 U	800	1000
1	4 464 13	42 U	800	1200
1	4 464 14	47 U	600	1000
1	4 464 15	47 U	600	1200
1	4 464 16	47 U	800	1000
1	4 464 17	47 U	800	1200

### Side panels for server cabinets

Set of 2, with plinths

Pack	Cat.Nos	Capacity	Depth (mm)
2	4 464 20	42 U	1000
2	4 464 21	42 U	1200
2	4 464 22	47 U	1000
2	4 464 23	47 U	1200

### LCS<sup>3</sup> Flatpack server cabinets, including side panels

Flatpack cabinets have the same configuration as Cat.Nos 4 464 02 and 4 464 03 respectively, only with side panels

Pack	Cat.Nos	Capacity	Width (mm)	Depth (mm)
1	4 464 25	42 U	800	1000
1	4 464 26	42 U	800	1200

### LCS<sup>3</sup> 19" cabling cabinets - 800 mm wide

Pack	Cat.Nos	Capacity	Width (mm)	Depth (mm)	Height (in mm)
1	4 464 30	24 U	800	800	1300
1	4 464 31	24 U	800	1000	1300
1	4 464 32	42 U	800	800	2000
1	4 464 33	42 U	800	1000	2000
1	4 464 34	47 U	800	800	2200
1	4 464 35	47 U	800	1000	2200