

Linkeo Data Center 19" server cabinets

cabinets and equipment



4 468 00



4 468 20



4 468 40



4 468 50



4 468 60




Technical characteristics p. 1035

Pack	Cat.Nos	19" server cabinets																											
		<p>19" freestanding server cabinets for data storage, server housing, infrastructural cabling and have also solutions for hot/cold corridor datacenter architecture</p> <p>IP 20 baying cabinets</p> <p>1500 kg load carrying capacity</p> <p>Equipped with 4 x 19" uprights with U marking and adjustable depth</p> <p>Pre-cut cable entries (top and bottom)</p> <p>Cut-out at the top for fan kit</p> <p>Black RAL 9005</p> <p>Complete server cabinets (ready assembled)</p> <p>Equipped with:</p> <ul style="list-style-type: none"> - Single front and rear microperforated 80% door - 2 side panels - levelling feet - grounding kit 																											
1	4 468 00	Capacity																											
1	4 468 01	42 U																											
1	4 468 02	42 U																											
1	4 468 03	42 U																											
1	4 468 04	47 U																											
1	4 468 05	47 U																											
1	4 468 06	47 U																											
1	4 468 07	47 U																											
		<table> <tr> <th>Height (mm)</th><th>Width (mm)</th><th>Depth (mm)</th></tr> <tr> <td>2052</td><td>600</td><td>1000</td></tr> <tr> <td>2052</td><td>600</td><td>1200</td></tr> <tr> <td>2052</td><td>780</td><td>1000</td></tr> <tr> <td>2052</td><td>780</td><td>1200</td></tr> <tr> <td>2274</td><td>600</td><td>1000</td></tr> <tr> <td>2274</td><td>600</td><td>1200</td></tr> <tr> <td>2274</td><td>780</td><td>1000</td></tr> <tr> <td>2274</td><td>780</td><td>1200</td></tr> </table>	Height (mm)	Width (mm)	Depth (mm)	2052	600	1000	2052	600	1200	2052	780	1000	2052	780	1200	2274	600	1000	2274	600	1200	2274	780	1000	2274	780	1200
Height (mm)	Width (mm)	Depth (mm)																											
2052	600	1000																											
2052	600	1200																											
2052	780	1000																											
2052	780	1200																											
2274	600	1000																											
2274	600	1200																											
2274	780	1000																											
2274	780	1200																											



Pack	Cat.Nos	Server cabinet frame																											
		<p>Cabinet frame without doors, side panels, levelling feet</p>																											
1	4 468 20	Capacity																											
1	4 468 21	42 U																											
1	4 468 22	42 U																											
1	4 468 23	42 U																											
1	4 468 24	47 U																											
1	4 468 25	47 U																											
1	4 468 26	47 U																											
1	4 468 27	47 U																											
		<table> <tr> <th>Height (mm)</th><th>Width (mm)</th><th>Depth (mm)</th></tr> <tr> <td>1967</td><td>600</td><td>1000</td></tr> <tr> <td>1967</td><td>600</td><td>1200</td></tr> <tr> <td>1967</td><td>780</td><td>1000</td></tr> <tr> <td>1967</td><td>780</td><td>1200</td></tr> <tr> <td>2189</td><td>600</td><td>1000</td></tr> <tr> <td>2189</td><td>600</td><td>1200</td></tr> <tr> <td>2189</td><td>780</td><td>1000</td></tr> <tr> <td>2189</td><td>780</td><td>1200</td></tr> </table>	Height (mm)	Width (mm)	Depth (mm)	1967	600	1000	1967	600	1200	1967	780	1000	1967	780	1200	2189	600	1000	2189	600	1200	2189	780	1000	2189	780	1200
Height (mm)	Width (mm)	Depth (mm)																											
1967	600	1000																											
1967	600	1200																											
1967	780	1000																											
1967	780	1200																											
2189	600	1000																											
2189	600	1200																											
2189	780	1000																											
2189	780	1200																											



Pack	Cat.Nos	Front or rear cabinets doors
		<p>DKP sheet metal</p> <p>80% perforations</p> <p>Can open 220°</p> <p>Equipped with locking mechanism (3 point lock) and hinge system</p> <p>Includes 1 piece of door with key</p> <p>Reversible single opening</p> <p>For cabinets 42 U - 600mm</p> <p>For cabinets 42 U - 780mm</p> <p>For cabinets 47 U - 600mm</p> <p>For cabinets 47 U - 780mm</p> <p>Double opening (in 2 parts)</p> <p>For cabinets 42 U - 600mm</p> <p>For cabinets 42 U - 780mm</p> <p>For cabinets 47 U - 600mm</p> <p>For cabinets 47 U - 780mm</p>
1	4 468 40	
1	4 468 41	
1	4 468 42	
1	4 468 43	
1	4 468 50	
1	4 468 51	
1	4 468 52	
1	4 468 53	



Pack	Cat.Nos	Cabinet side panels
		<p>Fixed to cabinet by cylindrical key lock</p> <p>Set of 2 side panels</p> <p>Side panel in 1 piece for 1000 mm deep cabinets</p> <p>Side panel in 2 pieces (half cabinet height) for 1200 mm deep cabinets</p> <p>For cabinets 42 U - 1000mm (1 part)</p> <p>For cabinets 42 U - 1200mm (2 parts)</p> <p>For cabinets 47 U - 1000mm (1 part)</p> <p>For cabinets 47 U - 1200mm (2 parts)</p>
1	4 468 60	
1	4 468 61	
1	4 468 62	
1	4 468 63	

