



4 468 70



4 468 91



4 468 95



4 469 01

Pack	Cat.Nos	Plinths
1	4 468 70	Metal plinths consisting of 4 corner blocks
1	4 468 71	Height: 100 mm
1	4 468 72	Width 600mm - depth 1000 mm
1	4 468 73	Width 600mm - depth 1200 mm
		Width 800mm - depth 1000 mm
		Width 800mm - depth 1200 mm
1	4 468 80	Casters and levelling kit
		Set of 4 casters
		Must be use with levelling feet
		Load capacity per caster: fixed (150 kg), moving (112 kg)
1	4 468 81	Levelling feet
		Set of 4 pcs
		Possible to adjust height of the feet from the floor
		Load capacity per levelling feet: 375 kg
1	4 468 86	Anti-tilt bar
		Bars provide a high level of stability for the products
1	4 468 87	Floor fixing kit
		Galvanised sheet metal
		4-points fixing between the cabinet and the floor - front/rear, right/left
		Must be use with casters and levelling feet
		Cabinets floor fixing kit
1	4 469 47	Baying kit
		Set of 2 pcs

Pack	Cat.Nos	Vertical patchcord manager
		To guide and manage the cords vertically
		Set of 2 pcs
		Compatible only with 800 mm wide cabinets
		Finger type
		Particularly suitable for optical cables
1	4 468 91	42 U
1	4 468 92	47 U
		Metal
		Particularly suitable for heavier cables
1	4 468 93	42 U
1	4 468 94	47 U
1	4 468 95	Cable tray
1	4 468 96	Perforated metal tray to fix cables on cabinet sides
		42 U - width 100 mm
		47 U - width 100 mm
		Fan modules
		4 or 6 pcs of fan on a module, with ON/OFF switch, analog thermostat functions
		Complete inner wiring
		230 V~
		Power supply cord 3 m
1	4 469 01	4 fans, 2P+E European standard (French - German standard) plug
1	4 469 02	4 fans, 2P+E British standard plug
1	4 469 03	6 fans, 2P+E European standard (French - German standard) plug
1	4 469 04	6 fans, 2P+E British standard plug
1	4 468 97	PDU holder
		To mount PDUs vertically
		To be fixed in the corner of the cabinet
		Set of 2 pcs, for 1 PDU
1	4 468 98	Grounding busbar kit
		6 pieces earthing leads + copper busbar