

# Power Distribution Units (PDU), Lincoo Data Center

## Basic and Basic with Local Power Meter



To provide ~ electric power for IT equipment in 19" enclosures  
 Equipped with hydraulic magnetic circuit protection with high current interruption capacity. Hydraulic magnetic circuit breakers are not affected by ambient temperature  
 330° rotating cable input for a perfect orientation of the cable and no interference in the cabinet  
 IEC 60320 C13 and C19 outlets. Each C13 and C19 outlets are numbered gradually from the input and equipped with cord locking system to avoid any accidental disconnection (100 Newton retention force)  
 High Density (HD) PDUs provide a high density of C13 outlets to optimize outlet quantity and PDU length  
 High ambient temperature rating: 55°C  
 Aluminium chassis  
 Zero-U PDUs for vertical mounting in the cabinet. Supplied with standard and button-type mounting brackets

Pack	Cat.Nos	Basic PDU	Pack	Cat.Nos	Basic HD PDU
1	6 469 60	<b>Single phase - 16 A</b> 230 V - 50/60 Hz power supply 18 C13 outlets + 4 C19 3 m power supply cord with IEC 60309 16A plug	1	6 469 71	<b>Single phase - 32 A</b> 230 V - 50/60 Hz power supply 24 C13 outlets + 12 C19 3 m power supply cord with IEC 60309 32A plug
1	6 469 61	20 C13 outlets + 4 C19 C20 inlet (can receive power cables Cat.Nos 6 469 05 and 6 469 06)	1	6 469 72	36 C13 outlets + 6 C19 3 m power supply cord with IEC 60309 32A plug
1	6 469 62	<b>Single phase - 32 A</b> 230 V - 50/60 Hz power supply 20 C13 outlets + 4 C19 3 m power supply cord with IEC 60309 32A plug	1	6 469 11	<b>Three phase - 16 A</b> 400 V - 50/60 Hz power supply 24 C13 outlets + 12 C19 3 m power supply cord with IEC 60309 16A plug
1	6 469 63	12 C13 outlets + 12 C19 3 m power supply cord with IEC 60309 32A plug	1	6 469 10	36 C13 outlets + 6 C19 3 m power supply cord with IEC 60309 16A plug
1	6 469 64	<b>Three phase - 16 A</b> 400 V - 50/60 Hz power supply 21 C13 outlets + 3 C19 3 m power supply cord with IEC 60309 16A plug	1	6 469 73	<b>Three phase - 32 A</b> 400 V - 50/60 Hz power supply 24 C13 outlets + 12 C19 3 m power supply cord with IEC 60309 32A plug
1	6 469 65	24 C13 outlets + 6 C19 3 m power supply cord with IEC 60309 16A plug	1	6 469 74	36 C13 outlets + 12 C19 3 m power supply cord with IEC 60309 32A plug
1	6 469 65	36 C13 outlets + 6 C19 3 m power supply cord with IEC 60309 16A plug	1	6 469 75	36 C13 outlets + 6 C19 3 m power supply cord with IEC 60309 32A plug
1	6 469 66	<b>Basic PDU with Local Power Meter</b> Local Power Meter module monitors voltage (V), current (A), active power (kW) and energy (kWh) Phase and circuits measurements: +/- 1% metering accuracy Data's display on SLCD screen Buzzer alarm Hot swappable architecture <b>Single phase - 32A</b> 230 V - 50/60 Hz power supply 20 C13 outlets + 4 C19 3 m power supply cord with IEC 60309 32A plug	1	6 469 70	<b>Basic HD PDU with Local Power Meter</b> Local Power Meter module monitors voltage (V), current (A), active power (kW) and energy (kWh) Phase and circuits measurements: +/- 1% metering accuracy Data's display on SLCD screen Buzzer alarm Hot swappable architecture <b>Three phase - 16 A</b> 400 V - 50/60 Hz power supply 36 C13 outlets + 6 C19 3 m power supply cord with IEC 60309 16A plug



**Configure To Order:** Need another configuration and/or functions ? Legrand is organized to configure PDUs as per your request. Please contact your sales representative

Red catalogue numbers: New products