

# Power Distribution Units (PDU), Linleo Data Center

accessories and Power cords



6 461 30



6 460 03



6 441 01



6 442 07

Pack	Cat.Nos	Accessories for metered and switched Intelligent PDUs
1	6 461 30	<b>Node PDU controller</b> Controller module Plug the controller on a base version of intelligent PDU to transform it into a node version <b>Wireless sensors</b> For cabinet environmental monitoring Easy wire-free deployment and maintenance Wireless communication with PDUs (2.4 GHz Zigbee Green Power) Ultra long battery life (5+ years replaceable battery) Different fixing solutions for sensors: with double sided tape, with cable ties, with a swing nut (supplied with the sensors) or with accessory Cat.No 6 460 06 for a more stylish installation
1	6 460 03	<b>Temperature &amp; Humidity wireless sensor</b> Monitors cool air entering and/or hot air being expelled, and optimizes your cooling infrastructure
1	6 460 04	<b>Contact closure wireless sensor</b> To be installed inside the rack to manage door contact sensors and alert in case of door opening/closing

Pack	Cat.Nos	Accessories for all PDUs
1	6 469 05	<b>Power cables</b> Cable IEC 60320 C19 to IEC 60309 16 A 2P+E plug Rotary locking mechanism on C19 plug that fits any standard C20 inlet to avoid accidental disconnection
1	6 469 06	
1	9 812 27	<b>Brackets</b> 1 set of Zero-U PDU mounting bracket for Nexpan rack
1	9 812 28	10 sets of Zero-U PDU mounting bracket for Nexpan rack
6	6 468 94	<b>Locking caps</b> To block the use of an outlet. A key is necessary to remove the cap and free the access Light grey RAL 7035
6	6 468 95	

Pack	Cat.Nos	Power cords C14 to C13 plugs
		Server side locking Unique rotary mechanism on C13 plug that fits any standard C14 inlet Set of 10
1	6 441 00	<b>Black</b> Length 0.5 m
1	6 441 01	Length 1 m
1	6 441 02	Length 1.5 m
1	6 441 03	Length 2 m
1	6 441 06	<b>Red</b> Length 0.5 m
1	6 441 07	Length 1 m
1	6 441 08	Length 1.5 m
1	6 441 09	Length 2 m
1	6 441 12	<b>Blue</b> Length 0.5 m
1	6 441 13	Length 1 m
1	6 441 14	Length 1.5 m
1	6 441 15	Length 2 m

Pack	Cat.Nos	Power cords C20 to C19 plugs
		Server side locking Unique rotary mechanism on C19 plug that fits any standard C20 inlet Set of 10
1	6 442 01	<b>Black</b> Length 1 m
1	6 442 02	Length 1.5 m
1	6 442 03	Length 2 m
1	6 442 07	<b>Red</b> Length 1 m
1	6 442 08	Length 1.5 m
1	6 442 09	Length 2 m
1	6 442 13	<b>Blue</b> Length 1 m
1	6 442 14	Length 1.5 m
1	6 442 15	Length 2 m