

Mosaic™ socket outlets



Pack	Cat.Nos		
			Sockets for installation on DLP trunking - German standard Mosaic sockets with shutters with connection at both sides for mounting on 65 and 85 mm cover DLP trunking in conjunction with supports and plates for trunking (see p. 1077) Direct connection requiring no tools, intuitive disconnection without dismantling the support
10	White 0 774 01	Tamperproof 0 774 21	Automatic terminals 2P+E
10	0 774 02	0 774 22	2 x 2P+E
10	0 774 03	0 774 23	3 x 2P+E
5	0 774 04	0 774 24	4 x 2P+E
10	Red 0 774 11		2P+E
10	0 774 12		2 x 2P+E
10	0 774 13		3 x 2P+E
5	0 774 14		4 x 2P+E
			Automatic terminals with cable grip
8	White 4 500 16	Tamperproof 4 500 18	2 x 2P+E
10	4 500 17	4 500 19	3 x 2P+E
			Automatic terminals - Wieland Equipped with fast connectors Wieland GST18i3
8	White 4 500 00	Red 4 500 02	2 x 2P+E
10	4 500 01	4 500 03	3 x 2P+E
			Automatic terminals - Wago Winsta Equipped with fast connectors Wago Winsta
8	4 500 04	4 500 06	2 x 2P+E
10	4 500 05	4 500 07	3 x 2P+E

Pack	Cat.Nos		
			Sockets for installation on DLP trunking - German standard (continued)
10	White 0 776 01	Tamperproof 0 776 21	Screw terminals 2P+E
10	0 776 02	0 776 22	2 x 2P+E
10	0 776 03	0 776 23	3 x 2P+E
5	0 776 04	0 776 24	4 x 2P+E
10	Red 0 776 11		2P+E
10	0 776 12		2 x 2P+E
10	0 776 13		3 x 2P+E
5	0 776 14		4 x 2P+E
			Accessories
10	0 502 99		Tamperproof insert for socket Fits directly into the plug
10	0 898 07		Cable grip