

Accessories for flexible cover universal DLP trunking



| Pack | Cat.Nos | Accessories |
|------|----------|--|
| 1 | 0 306 98 | Cutting accessories for trunking DLPlus cutting unit for PVC DLP For cutting all plastic bodies Avoids vibration when cutting bases and covers. Aluminium Dim.: 225 x 142 x 76 mm |
| 10 | 0 304 18 | Insulation accessory Base joint. Adjustable wall insulation joint, supplied in 5 m lengths Provides continuity between the trunking and the wall, in particular in internal angles |
| | | Fixing accessories for trunking For fixing all plastic profiles Wall plugs for immediate fixing No screws or nails required |
| 100 | 0 308 98 | For mini-trunking |
| 100 | 0 308 99 | For mini-trunking, skirting trunking and trunking |
| 12 | 0 309 49 | Cartridge of Neoprene Adhesive for glue gun |
| 200 | 0 308 97 | DLP rapid wall plug For 10 mm min. plasterboard walls at least 20 mm away from the concrete surface For fixing DLP plastic trunking in a single operation Used with a special tool for drill (Ø8 mm), supplied in each pack of 200 wall plugs Tensile resistance: 25 kg |
| 100 | 0 106 95 | Spit end cap for DLP trunking For rapid fixing of trunkings with the Spit Pulsa 700 E (use 20 mm Spit nails) |
| | | Junction boxes for DLP trunking Fitted with current separator Cable entry possible via the bottom of the box |
| 10 | 0 313 50 | White junction boxes Dim.: 163 x 163 x 65 mm (except profile height 80 mm) |
| 5 | 0 313 51 | Dim.: 200 x 200 x 83 mm |
| 5 | 0 313 52 | Dim.: 250 x 250 x 83 mm |
| | | VDI cable management accessories To be fitted on the standard accessories (angles and junctions). For all trunking sizes except 35 x 80 trunking and in compartments with 40 mm width cover |
| 5 | 0 107 80 | Accessory for internal angle |
| 5 | 0 107 81 | Accessory for external angle |
| 5 | 0 107 82 | Accessory for flat angle |
| 5 | 0 107 83 | Accessory for flat junction |

| Pack | Cat.Nos | Accessories |
|------|-----------|--|
| 10 | 0 343 98 | Base for Nybloc auto terminals For up to 3 screwless connection terminals Nybloc auto (Cat.Nos 0 343 22/23/25/28) Direct fixing: - in top of Plexo boxes and industrial plastic cabinets ≥ 130 x 130 mm - on flat bar 12 x 2 mm - in bottom of universal and aluminium DLP trunkings (from 50 x 80 mm) Screw fixing: - in bottom of Plexo boxes ≥ 105 x 105 mm and industrial plastic cabinets - universal Fixing on rail with accessory Cat.No 0 048 11 (p. 298) Accessible test socket Marking zone with felt tip pen Cat.No 0 395 98 (p. 451) |
| 20 | 0 312 10 | Connection strips Connection strips with 4 x 4 mm ² terminals for junction boxes |
| 100 | 0 308 81 | For high current cables Base for cable ties |
| | | Flat junctions Base junctions To tap-off to a profile smaller than 50 x 105 To tap-off to an 80 mm width trunking |
| 10 | 0 107 32 | To tap-off to a profile smaller than 50 x 105 |
| 5 | 0 107 33 | |
| | | Accessories for separation partition Allow bottom compartment cables to pass through the separation partition in case of a flat junction |
| 5 | 0 107 42 | For 50 mm height separation partition |
| 5 | 0 107 43 | For 65 mm height separation partition |
| | | Junctions for change of plane To tap-off from wall to ceiling, for example to supply power to a luminaire |
| 5 | 0 107 71 | For cover 65 mm |
| 5 | 0 107 72 | For cover 85 mm |
| 5 | 0 107 73 | For trunking Cat.No 0 104 24 |
| | | Junctions between floor duct and trunking To tap-off to floor duct Cat.No 0 328 00 (p. 1133) |
| 5 | 0 107 71+ | For cover 65 mm |
| 5 | 0 106 90 | For cover 85 mm |
| 5 | 0 107 72+ | |
| 5 | 0 106 90 | |
| | | Wall feedthroughs Provides a finish between the trunking and the wall |
| 5 | 0 106 98 | For trunking 80 to 150 mm width |
| 5 | 0 106 99 | For trunking 195 to 220 mm width |