

# Incara™ Disq 60 - German standard

for offices and collaborative spaces



Technical characteristics p. 1100

For flush-mounting in furniture in Ø60 mm cut-out  
 Three methods of installation:  
 - Flush-mounting in the furniture (desk), 6-40 mm thickness  
 - Flush-mounting on a soft surface (armchair, sofa) using a dedicated accessory  
 - Flush-mounting on a metal panel, 1 mm thickness (locker)

Pack	Cat.Nos	2P+E flush sockets
		16 A 250 V~ 50/60 Hz Sockets specially designed for passageways (30,000 operations) and equipped with safety shutters Conform to standard IEC 60884-1
1	6 547 27F	<b>With 0.5 m cord and GST18i3 Wieland connector</b>
1	6 547 25F	● Metal finish
1	6 547 26F	○ White finish
		● Black finish
1	6 547 27	<b>With 2 m cord and 2P+E plug</b>
1	6 547 25	● Metal finish
1	6 547 26	○ White finish
		● Black finish

Pack	Cat.Nos	2P+E flush sockets with metal cover
		16 A 250 V~ 50/60 Hz Sockets specially designed for passageways (30,000 operations), equipped with safety shutters Conform to standard IEC 60884-1 Swivel cover For protection and a neat and stylish appearance
1	6 547 28F	<b>With 0.5 m cord and GST18i3 Wieland connector</b>
		● Metal cover
1	6 547 28	<b>With 2 m cord and 2P+E plug</b>
		● Metal cover

Pack	Cat.Nos	15 W USB Type-A + Type-C chargers
		Power supply: 110-240 V~ 50/60 Hz Conform to standard IEC 62368-1
1	6 547 32F	<b>With 0.5 m cord and GST18i3 Wieland connector</b>
1	6 547 30F	● Metal finish
1	6 547 31F	○ White finish
		● Black finish
1	6 547 32	<b>With 2 m cord and 2P+E plug</b>
1	6 547 30	● Metal finish
1	6 547 31	○ White finish
		● Black finish

Pack	Cat.Nos	15 W USB Type-A + Type-C chargers with cover
		Power supply: 110-240 V~ 50/60 Hz Conform to standard IEC 62368-1 Swivel cover for protection and a neat and stylish appearance
1	6 547 33F	<b>With 0.5 m cord and GST18i3 Wieland connector</b>
		● Metal cover
1	6 547 33	<b>With 2 m cord and 2P+E plug</b>
		● Metal cover
15	6 547 39	<b>Accessory for installing in a soft surface</b> For strengthening the fabric cover to provide stability for the product
		<b>Wieland accessories</b>
1	6 549 86	<b>Combined Wieland GST18i3 connector/2P+E plug cord</b> Length 2 m
1	6 549 87	Length 3 m
1	6 547 99	<b>Protective casing</b> For Wieland GST18i3 connectors

Other configurations, socket standards and finishes available on request or via the pCon software

