

Snap-on columns (continued)




Conform to IEC 61084-2-1 and EN 50085-2-4
For distribution of power vertically
Power supply via the ceiling and/or the floor
Cover width 45 mm

Pack	Cat.Nos	Ovaline column
1	6 530 54	Aluminium finish Complete Ovaline column, height 3.2 m
1	6 530 55	Ovaline tube, height 3.2 m
1	6 530 58	Ovaline junction 90°
1	6 530 59	Ovaline fixing bracket
1	6 530 57	Cable output for Ovaline column

Finishing kit for telescopic pole for 1 or 2 compartments columns

1	6 530 66	White finish
1	6 530 67	Aluminium finish
1	6 530 68	Black finish



Accessories for columns

1	6 530 56	Flexible Ovaline kit For horizontal connection to cable trays Length: 1 m
36	6 038 07	Supplied with fixing bracket Separation partition, height 60 mm For 2 and 4 compartments snap-on columns and mini-columns
1	6 530 80	Panel indicator 150 x 150 mm
1	6 530 83	Shelf for direct clipping

Supports for rail equipment (columns and mini-columns)

5	0 310 69	White finish
5	0 307 87	Aluminium finish
5	6 530 75	Black finish



90° adaptor

5	6 530 79	Adaptor for mounting Arteor or Mosaic wiring accessories horizontally via 90° rotation 2 modules
---	----------	---



Multi-support sockets - German standard socket outlets, USB charging socket, HDMI type A socket



Particularly suitable for installation in snap-on columns and mini-columns, pop-up flush-mounting boxes for furniture (p. 1103)

Multi-support German standard socket outlets - inclined 45°

Pack	Cat.Nos	Multi-support German standard socket outlets - inclined 45°
10	Matt Black 0 793 55L	Automatic terminals 2P+E
10	0 793 72L	2 x 2P+E
10	0 793 73L	3 x 2P+E

RJ 45 data sockets

10	Matt Black 0 794 61L	Cat 6 UTP 1 module
10	0 791 65L	Cat 6 FTP 2 modules
10	0 791 76L	Cat 6 STP 2 modules

Double USB Type A charging socket

1	Matt Black 0 791 94L	5 V - 3 A - 2 modules For recharging portable devices like: telephones, smartphones, MP3/MP4 players and fast-charging tablet PC Conform to IEC 62684-2011-01 Consumption in passive mode < 0.07 W Supplied cordless
---	-------------------------	--

HDMI Type A socket

1	Matt Black 0 794 78L	Preterminated HDMI - version 2.0 - 1 module. Equipped with cord, length 15 cm and 2 female connectors. Used to transmit high-definition digital audio/video streams between a cours (computer, Blu-ray player...) and a compatible receiver. Can be associated with HDMI cord & cable
---	-------------------------	---

Fixing clip

10	6 038 56	For 45 mm wiring devices, like Mosaic and Arteor With anti-pullout and anti-slip system for perfect fitting of the mechanisms on : DLP-S and DLP aluminium snap-on trunking and snap-on columns and mini-columns Black finish
----	----------	---



Other Mosaic socket outlets,
p. 1182-1183

