

## Mosaic™ mechanisms

### pull-cord switches and ventilation control



0 770 14



0 770 27L



0 791 27L



Selection chart for boxes, supports and plates **p. 1198-1199**

All two-way switches with indicator have a terminal for neutral connection and must be equipped with an indicator

Pack	Cat.Nos	Pull-cord switches
1	0 770 14	Fast connection via automatic terminals, no tool required <b>Two-way switch, 10 AX - 250 V~ - 2 modules</b> For controlling incandescent and halogen lamps up to 2300 W ○ White With cord length 1.5 m
1	0 770 44	<b>Two-way push-button - 6 A - 250 V~ , with pull cord - 2 modules</b> ○ White With cord length 1.5 m
1	0 770 27L	<b>Ventilation control</b> Fast connection via automatic terminals, no tool required <b>Two-way switch</b> For direct control of controlled mechanical ventilation 10 AX - 250 V~ ○ White antimicrobial <sup>(1)</sup> ● Matt Black
1	0 791 27L	

1: Contains a silver compound to prevent the growth of bacteria on the surface of the plate

## Mosaic™ mechanisms

### skirting light with motion sensor



0 785 11

Pack	Cat.Nos	Skirting light with motion sensor
1	0 785 11	Mechanism equipped with an infrared detection cell and a LED beam To be installed close to the floor (next to a socket, for example) When someone passes, the mechanism detects movement and switches the light on Ideal to illuminate a corridor at night without dazzling people, or to highlight possible danger Equipped with an audible signal that can be deactivated (when product is used for lighting) or not (so as to indicate danger) Detection field: 180° Range: 6m 2 modules ○ White

