

Mosaic™ mechanisms

RJ 45 sockets - Cat. 6



Selection chart for boxes, supports and plates **p. 1198-1199**

Can be integrated in all supports (p. 1198-1199)
 Mechanisms to be equipped with support frames and plates
 Equipped with connectors with quick toolless connection
 Take single-core cables from AWG 22 up to AWG 26, and AWG 26 multicore cables
 T568A and B marking with colour codes
 Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards

| Pack | Cat.Nos | Cat. 6 RJ 45 sockets (continued) |
|------|----------|---|
| 5 | 0 765 95 | FTP with controlled access - 2 modules Supplied with 2 keys for 5 sockets ○ White with red shutter |
| 10 | 0 765 05 | FTP 45° - 2 modules ○ White |
| 5 | 0 765 06 | FTP 2 x RJ 45 45° - 2 modules ○ White |
| 1 | 0 765 33 | FTP retractable RJ 45 sockets - 4 modules With integrated retractable cord (0.9 m) Winds up automatically with a push-button ○ White ● Alu |
| 1 | 0 794 33 | |
| 10 | 0 765 92 | FTP 90° - 2 modules Vertical snap-on socket for column module ○ White ● Alu |
| 10 | 0 794 92 | |
| 10 | 0 765 63 | Shielded STP - 1 module ○ White ○ White antimicrobial ⁽¹⁾ |
| 10 | 0 765 83 | |
| 10 | 0 765 66 | Shielded STP - 2 modules ○ White |
| 5 | 0 765 96 | Shielded STP with controlled access - 2 modules Supplied with 2 keys for 5 sockets ○ White with red shutter |
| 10 | 0 765 07 | STP 45° - 2 modules Vertical snap-on socket for column module ○ White |
| 10 | 0 765 93 | Shielded STP 90° - 2 modules Vertical snap-on socket for column module ○ White |

1: Contains a silver compound which prevents the growth of bacteria at the surface

Mosaic™ mechanisms

RJ 45 sockets - Cat. 5e



Selection chart for boxes, supports and plates **p. 1198-1199**

Can be integrated in all supports (p. 1198-1199)
 Mechanisms to be equipped with support frames and plates
 Equipped with connectors with quick toolless connection
 Take single-core cables from AWG 22 up to AWG 26, and AWG 26 multicore cables
 T568A and B marking with colour codes
 Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards

| Pack | Cat.Nos | Cat. 5e RJ 45 sockets |
|------|----------|--|
| 10 | 0 765 51 | UTP - 1 module ○ White ● Alu |
| 10 | 0 794 51 | |
| 10 | 0 765 54 | UTP - 2 modules ○ White ● Alu |
| 10 | 0 794 54 | |
| 10 | 0 765 97 | UTP with controlled access - 2 modules Supplied with 2 keys for 5 sockets ○ White with red shutter |
| 5 | 0 765 41 | UTP - 2 x RJ 45 with Soluclip accessory - 3 modules For snap-on mounting on DLP trunking with 45 mm cover ○ White |
| 1 | 0 765 30 | UTP retractable RJ 45 socket - 4 modules With integrated retractable cord (0.9m) Winds up automatically with a push-button ○ White |
| 10 | 0 765 01 | UTP 45° - 2 modules ○ White |
| 5 | 0 765 02 | 2 x RJ 45 UTP 45° - 2 modules ○ White |
| 10 | 0 765 52 | FTP - 1 module ○ White ● Alu |
| 10 | 0 794 52 | |
| 10 | 0 765 55 | FTP - 2 modules ○ White ● Alu |
| 10 | 0 794 55 | |
| 10 | 0 765 98 | FTP with controlled access - 2 modules Supplied with 2 keys for 5 sockets ○ White with red shutter |
| 5 | 0 765 42 | FTP - 2 x RJ 45 with Soluclip accessory - 3 modules For snap-on mounting on Mosaic trunking with 45 mm cover ○ White |