

Mosaic™ mechanisms

audio and video sockets



Selection chart for boxes, supports and plates **p. 1198-1199**
Installation principle **p. 1195**

Pack	Cat.Nos	HDMI type A sockets
		Used to transmit high-definition digital audio/video streams between a source (computer, Blu-ray player...) and a compatible receiver (TV, videoprojector...) Maximum distance between 2 sockets: 10m
		Preterminated - 2.0 - 1 module Equipped with cord, length 15 cm
1	0 787 78	○ White
1	0 793 78	● Alu
1	0 794 78L	● Matt Black
		Preterminated - 2.0 - 2 modules Equipped with cord, length 15 cm
1	0 789 79L	○ White
1	0 792 79L	● Alu
1	0 794 79L	● Matt Black
		HDMI extender
1	0 517 38	Used to connect remote HDMI terminals up to 60 m The kit comprises transmitter and receiver units as well as power supplies The transmitter and receiver are linked by an RJ 45/RJ 45 cable (not supplied) Compatible with 4K, 3D, EDID and HDCP Including infrared control Certified HDBaseT

Pack	Cat.Nos	Display port sockets
		Used to transmit high-definition digital audio/video streams between a source (laptop, computer, etc) and a compatible receiver (videoprojector, TV...) Maximum distance between 2 sockets: 10m
		Preterminated socket - 1 module Equipped with cord, length 15 cm
1	0 787 91	○ White
		HD15 sockets
		Used to transmit analog video streams (VGA, XGA, UXGA depending on graphic card) between a source (computer) and a compatible receiver (video projector, TV...) Maximum distance between 2 sockets: 15m
		Preterminated socket - 1 module Equipped with cord, length 15 cm
1	0 787 77	○ White
1	0 793 77	● Alu
		Screw-type socket - 2 modules
1	0 787 57	○ White
		Screw-type socket + 3.5 mm Jack - 2 modules
1	0 787 74	○ White