










Mosaic™ mechanisms

audio and video sockets (continued)



Selection chart for boxes, supports and plates p. 1198-1199

Pack	Cat.Nos		
		Videoprojector switch	
1	0 787 99	Universal remote switch allowing to turn ON or place in STANDBY mode a video projector To be installed with a push-button Works with all videoprojectors or TV through IR learning process Installed close to the room's lighting switches, it replaces the constructors remote and fosters the ignition and extinction of the video projector therefore reducing energy consumption and extending the bulb's lifetime 2 modules  ○ White	
		Jack sockets 3.5 mm	
1	0 787 79	3.5 mm Jack connectors can be used to create audio/video links	
1	0 793 79	Preterminated sockets - 1 module	
1	0 795 79L	Equipped with cord, length 15 cm  ○ White ● Alu ● Matt Black	
1	0 787 64	4 screw-type female 3.5 mm Jack socket - 1 module	
1	0 795 64L	○ White ● Matt Black	
1	0 787 73	Solder-type female 3.5 mm Jack socket - 1 module	
		○ White	
		Female 2 RCA sockets	
1	0 787 47	Provide the stereo audio link for any peripheral device such as a DVD drive, camera, video recorder 1 module Preterminated Equipped with a 15 cm cord  ○ White	
1	0 787 53	Connection via screw terminals	
		○ White	
		Female 3 RCA sockets	
1	0 787 54	Provide the composite video and stereo audio links for any peripheral device such as a DVD drive, camera, video recorder, videoconferencing, etc Connection via screw terminals 1 module  ○ White	
1	0 792 54	● Alu	
		3-pole XLR sockets	
1	0 787 55	Provide the stereo link for microphone, amplifier, mixing console, etc. Recommended cable: 1 audio pair 0.14 mm ² to 0.5 mm ² shielded Max. cable length: 50 m (without amplifier) 2 modules  ○ White - fast screw connection female	
1	0 792 55	● Alu - fast screw connection female	
1	0 795 55L	● Matt Black - fast screw connection female	
1	0 787 56	○ White - fast screw connection male	
		4-pole Speakon	
1	0 787 60	Used to connect power enclosures Recommended cable: 2 audio pairs 4 mm ² Max. cable length: 50 m (without amplifier) 2 modules  ○ White - fast screw connection female	
		Loudspeaker sockets	
10	0 787 51	Terminal 4 mm ²  ○ White - 2 modules	
10	0 795 51L	● Matt Black - 2 modules	
10	0 787 50	○ White - 1 module	
10	0 792 50	● Alu - 1 module	
10	0 795 50L	● Matt Black - 1 module	
		Attenuator	
1	0 787 76	100 V - 25 W Allows to adjust power to 25 W from a balanced 100 V loudspeaker line 2 modules  ○ White	
		Female BNC 75 socket	
1	0 787 58	Provides the composite video link for any peripheral device such as a DVD drive, camera, video recorder, etc 1 module  ○ White	