













































Mosaic™

with antimicrobial⁽¹⁾ treatment mechanism and plate selection chart

Control units		ELV sockets			
	Cat.Nos 0 766 77 0 783 76	Pull-cord mechanisms 2 A - 230 V Switch with ejectable pull cord - 1 module. White Push-button with ejectable pull cord - 1 module White		Cat.Nos 0 782 41	Magnetic connection sockets For nurse call unit (call only) - 2 modules White
	0 787 10L	Easy-Led two-way switches 10 AX - 250 V~ Two-way switch - 1 module White		0 782 45	For nurse call unit (call, lighting, shutters) - 2 modules White
	0 787 11L	Two-way switch - 2 modules White		0 765 84	RJ 45 sockets Cat. 6A shielded STP - 1 module - White
	0 787 14L	Easy-Led push-buttons 6 A - 250 V~ Push-button - 1 module White		0 765 83	Cat. 6 shielded STP - 1 module - White
	0 787 15L	Push-button - 2 modules White		0 765 82	Cat. 6 shielded FTP - 1 module - White
	0 770 43L	Two-way pushbutton with label-holder - 2 modules White		0 765 81	Cat. 6 shielded UTP - 1 module - White
	0 770 27L	Ventilation control Ventilation control - 2 modules White	Indication		
	0 766 66L	Touchless switches for lights 2 modules - White		0 785 01	Single indicators 230 V (1 W) - 1 module
	0 766 67L	2 modules - Matt Black		0 785 51	12-24 V (0.2 W) - 1 module
	0 766 95L	2 modules - White (plate supplied)		0 785 02	Double indicators 230 V (1 W) - 1 module
	0 766 80L	Touchless switches for doors 2 modules - White		0 785 52	12-24 V (0.2 W) - 1 module
	0 766 81L	2 modules - Matt Black		0 785 10	Illuminated signalling 230 V (0.2 or 1 W) 2 modules
	0 766 96L	2 modules - White (plate supplied)	Blanking plates		
	0 787 09	Touch control units Switch with neutral - 2 modules White		0 787 20	Blanking plate - 1 module - White
	0 787 05	Roller shutter switch Roller shutter switch - 2 modules White		0 787 21	Blanking plate - 2 modules - White
Mains voltage sockets		Plates			
	0 772 16	2P+E German standard sockets 2P+E socket - 2 modules - Green		0 787 22L	2 modules 2 modules - White
	0 772 17	2P+E socket - 2 modules - Orange		0 788 80	2 IP 44 modules - White
	0 772 20	2P+E socket - 2 modules - Red - Screw terminals		0 787 24L	4 modules 4 modules - horizontal - White
	0 787 02	2P+E socket - 2 modules - White - Screw terminals		0 787 25L	2 x 2 modules horizontal 2 x 2 modules - horizontal - White
	0 772 12	2P+E socket - 2 modules - White		0 787 23L	2 x 2 modules vertical 2 x 2 modules - vertical - White
	0 787 00	Equipotential sockets Equipotential socket - 1 module White		0 787 26L	6 modules horizontal 6 modules - horizontal - White
	0 787 60L	Equipotential socket - 2 modules White			
	0 772 19	2P+E socket with shutter - 2 modules - White			
	0 771 50	2P ELV sockets 2P ELV socket - 1 module - White			
	0 770 80	Anti-extraction module Anti-extraction module - 1 module - White			

1: Contains a silver compound to prevent the growth of bacteria on the surface of the plate