

Mosaic™ nurse call units

for day hospitals, dialysis centres...



0 782 14 + 0 766 60



0 782 04L



0 782 01







Selection chart for boxes, supports and plates **p. 1198-1199**

Designed for nurse call equipment in day hospitals, dialysis and transfusion centres, scanners, etc.

Functions:

- from the room: calls, emergency calls, nurse present indicator and call cancelling
- from the nurses' station: patient reassurance

Possibility of adding a paging system

Pack	Cat.Nos	Display units and management
1	0 766 60	6-direction call display unit  Registration of calls via numbered indicator lights and audible signal Several calls can be registered simultaneously Display of reassurance indicator and nurse present Possibility of transferring calls to 4 other display units (e.g.: treatment room, rest area, etc.) Installed: - in surface mounting box Cat.No 0 802 86 - on table control unit Cat.No 0 782 14 6 modules
1	0 782 14	Table control unit  Takes up to 6 display units Cat.No 0 766 60 Horizontal or vertical mounting Dim.: 310 x 295 x 75 mm 36 modules
1	0 782 89	24 V - 2 A - 48 W power supply  Powers the system If necessary, a 24 V protected power supply can be used 8 modules
1	0 782 12	3-direction management module  Manages 3 rooms (or directions) Possibility of forwarding via NO volt-free contact for indicator, audible signal, paging, master indicator 4 modules
Corridor and room equipment Supplied with metal support for screw mounting and white finishing plate 2 modules Can be flush or surface mounted Fitted with long life LEDs		
1	0 766 72L	Double display corridor overdoor light unit  Double indicator (red/white) Displays calls and nurse present in the corridor
1	0 782 04L	Door unit  Door unit including 1 red indicator, 1 white indicator and 1 call and nurse presence cancel push-button Antimicrobial ⁽¹⁾

Pack	Cat.Nos	Equipped hand-held remote control units
		IP 67 waterproof. White antimicrobial ⁽¹⁾ Red indicator visible at night via 2 illuminated LEDs Magnetic connection between hand-held remote control unit and socket Designed ergonomically for ease of handling. Can be ejected in all directions with pull-out torque designed to avoid any damage to the equipment Fitted with a 2.5 m cord Compatible with Programme Mosaic and other call systems on the market
1	0 782 01	For call only Equipped with 1 call button and red indicator for call confirmation For use in conjunction with socket Cat.No 0 782 46
1	0 782 02	For call and lighting control Equipped with: - 1 call button and red indicator for call confirmation - 1 button for reading light control - 1 button for room light control For use in conjunction with socket Cat.No 0 782 47
1	0 782 03	For calls and controlling lighting and roller shutters Equipped with: - 1 call button and red indicator for call confirmation - 1 button for reading light control - 1 button for room light control, - 2 buttons for controlling roller shutters - 1 free function button (example: switched socket) For use in conjunction with socket Cat.No 0 782 47
1	0 782 41	Sockets for hand-held remote control units Non indexed magnetic connection socket for hand-held remote control units Cat.Nos 0 782 01/81
1	0 782 45	Magnetic connection socket for hand-held remote control units Cat.Nos 0 782 02/03/82/84
5	0 782 43	Accessory for hand-held remote control units Clamp for holding the hand-held remote control unit within rzeach: on beds, clothes, armchairs, edge of beds, etc.

¹: Contains a silver compound to prevent the growth of bacteria on the surface of the plate