

# steel perimeter trunking selection chart

110 x 63 mm / 130 x 63 mm / 170 x 63 mm / 170A x 63 mm

Type	Trunking body	Lid	Accessory spacer lid	Couplers <sup>1</sup> (Supplied in pairs)
	Length 3 m	Length 1-5 m	Length 100 mm	
110 x 63 mm 	MP351233	MP351230	MP351220	MP351523
130 x 63 mm 	MP351235	MP351230	MP351220	MP351525
170 x 63 mm 	MP351236	MP351230	MP351220	MP351526
170A x 63 mm 	MP351237	MP351230	MP351220	MP351527

Type	Flat bend body rising	Flat bend body descending	Tee body <sup>4</sup>	Tee body rising <sup>4</sup>	Tee cover strap
110 x 63 mm 	-	-	MP351393	-	MP351563
130 x 63 mm 	-	-	MP351395	-	MP351565
170 x 63 mm 	-	-	MP351396	-	MP351566
170A x 63 mm 	MP351337	MP351367	-	MP351397	MP351567 <sup>2</sup> MP351597 <sup>3</sup>

Type	Riser trunking lid	Earthing wire	Universal snapper clip <sup>1</sup>	Divider <sup>1</sup>	Base divider <sup>1</sup>	Base divider fixing bracket <sup>1</sup>
				1 m	2 m	
				Regular power and data separation	Additional partition for the base	
110 x 63 mm 	MP351439	MP351499	MP351319	MP351189	-	-
130 x 63 mm 	MP351439	MP351499	MP351319	MP351189	MP351279	MP351299
170 x 63 mm 	MP351439	MP351499	MP351319	MP351189	MP351289	MP351309
170A x 63 mm 	MP351439	MP351499	MP351319	MP351189	MP351289	MP351309

1 : Internal components supplied unpainted 2 : Rising to 170 mm wide trunking

3 : Rising to 130 mm wide trunking 4 : Crossover available on request, please contact us on +44 (0)370 608 9020

<b>Universal internal/external bend lid 90° +/- 5°</b> 	<b>Internal bend cover straps 135°- 180°</b> 	<b>Internal bend body</b> 	<b>External bend body</b> 	<b>External bend lid</b> 	<b>Flat bend body</b> 	<b>Flat bend lid</b> 
MP351173	MP351203	MP351273	MP351303	MP351240	MP351333	MP351260
MP351175	MP351205	MP351275	MP351305	MP351240	MP351335	MP351260
MP351176	MP351206	MP351276	MP351306	MP351240	MP351336	MP351260
MP351177	MP351207	MP351277	MP351307	MP351240	-	MP351260
<b>End cap</b> 	<b>Cover strap</b> 	<b>Tolerance cover strap</b> 	<b>Wall flange plate</b> 	<b>Wall flange closing plate</b> 	<b>Support flange</b> 	<b>Riser trunking body<sup>1</sup> (170 x 38 mm)</b> 
MP351043	MP351103	MP351073	MP351483	MP351513	MP351453	MP351409
MP351045	MP351105	MP351075	MP351485	MP351515	MP351455	MP351409
MP351046	MP351106	MP351076	MP351486	MP351516	MP351456	MP351409
MP351046	MP351107	MP351077	MP351486	MP351516	MP351456	MP351409
<b>Internal lid support<sup>1</sup></b> 	<b>Internal bend lid</b> 	<b>End support bracket<sup>1</sup></b> 	<b>Tee support bracket<sup>1</sup></b> 	<b>Acoustic insulation block</b> 	<b>Cutting support block</b> 	<b>Touch-up paint</b> 
<b>IP 40 / IK 07</b>						
MP351469	MP351250	MP351449	MP351459	MP351389	MP351533	MP351029
MP351469	MP351250	MP351449	MP351459	MP351389	MP351535	MP351029
MP351469	MP351250	MP351449	MP351459	MP351399	MP351536	MP351029
MP351469	MP351250	MP351449	MP351459	MP351399	MP351536	MP351029