

steel perimeter trunking system – 110 x 63 mm

for dado applications (continued)



Selection charts **p. 4-5**
Dimensions and technical information **p. 16-19**
Installation material **p. 19**

Pack	Cat. Nos.	Fittings (continued)	Pack	Cat. Nos.	Regular power and data separation
1	MP351043	End cap ⁽¹¹⁾	20	MP351319	Universal snapper clip ¹ ⁽¹⁸⁾ Multifunction clip for fitting of divider, separation of cables (50 mm) and additional support of lid
10	MP351103	Cover strap ⁽¹²⁾ Width – 25 mm	10	MP351189	Divider ¹ ⁽²⁰⁾ Requires universal snapper clip Cat. No. MP351319 Length – 1 m
8	MP351073	Tolerance cover strap ⁽¹³⁾ Width – 40 mm	1	MP351469	Additional products IP 40 / IK 07 Internal lid support ¹ Fits inside lid joints to achieve IP 40
1	MP351483	Wall flange plate ⁽¹⁴⁾	1	MP351250	Internal bend lid To achieve IP 40 on internal bends
1	MP351513	Wall flange closing plate ⁽¹⁵⁾	5	MP351449	End support bracket ¹ Provides additional lid support at end of run Use to achieve IK 07
1	MP351453	Support flange	5	MP351459	Tee support bracket ¹ Fits inside lid joints to achieve IP 40 at tee junction
1	MP351409	Riser trunking body 170 x 38 mm ¹ ⁽¹⁶⁾ Pre-galvanised Length – 2 m	1	MP351389	Accessories Acoustic insulation block ⁽¹⁹⁾ For use when trunking passes through walls to reduce noise travel Self extinguishing plastic Acoustic tested according to NEN 5077/ISO 140/4
1	MP351439	Riser trunking lid ⁽¹⁷⁾ Friction fit Length – 1 m	1	MP351533	Cutting support block Holds trunking in position and guides saw for a straight cut Steel
1	MP351499	Earthing wire Length – 300 mm	1	MP351029	Touch-up paint Contents – 10 ml

1: Internal components supplied unpainted