

# steel perimeter trunking system – 130 x 63 mm

for dado applications (continued)



MP351235

MP351335

MP351395

MP351045

MP351105

MP351075

Selection charts **p. 4-5**  
Dimensions and technical information **p. 16-19**  
Installation material **p. 19**

| Pack | Cat. Nos. | Fittings (continued)   |
|------|-----------|--|
| 1    | MP351045  | <b>End cap</b> <sup>(11)</sup>   |
| 10   | MP351105  | <b>Cover strap</b> <sup>(12)</sup><br>Width – 25 mm                                      |
| 8    | MP351075  | <b>Tolerance cover strap</b> <sup>(13)</sup><br>Width – 40 mm                            |
| 1    | MP351485  | <b>Wall flange plate</b> <sup>(14)</sup>   |
| 1    | MP351515  | <b>Wall flange closing plate</b> <sup>(15)</sup>   |
| 1    | MP351455  | <b>Support flange</b>  |
| 1    | MP351409  | <b>Riser trunking body 170 x 38 mm</b> <sup>(16)</sup><br>Pre-galvanised<br>Length – 2 m |
| 1    | MP351439  | <b>Riser trunking lid</b> <sup>(17)</sup><br>Friction fit<br>Length – 1 m                |
| 1    | MP351499  | <b>Earthing wire</b><br>Length – 300 mm  |

| Pack | Cat. Nos. | Regular power and data separation  |
|------|-----------|--|
| 20   | MP351319  | <b>Universal snapper clip</b> <sup>(18)</sup><br>Multifunction clip for fitting of divider, separation of cables (50 mm) and additional support of lid   |
| 10   | MP351189  | <b>Divider</b> <sup>(20)</sup><br>Requires universal snapper clip<br>Cat. No. MP351319<br>Length – 1 m   |
| 10   | MP351279  | <b>Additional partition for the base</b><br><b>Base divider</b> <sup>(1)</sup><br>Fixing bracket required (below)<br>Length – 2 m<br>Height – 22 mm, for type 130  |
| 10   | MP351299  | <b>Base divider fixing bracket</b> <sup>(1)</sup><br>Height – 21 mm, for type 130<br>1 per metre required  |
| 1    | MP351469  | <b>Additional products IP 40 / IK 07</b><br><b>Internal lid support</b> <sup>(1)</sup><br>Fits inside lid joints to achieve IP 40  |
| 1    | MP351250  | <b>Internal bend lid</b><br>To achieve IP 40 on internal bends   |
| 5    | MP351449  | <b>End support bracket</b> <sup>(1)</sup><br>Provides additional lid support at end of run<br>Use to achieve IK 07   |
| 5    | MP351459  | <b>Tee support bracket</b> <sup>(1)</sup><br>Fits inside lid joints to achieve IP 40 at tee junction   |
| 1    | MP351389  | <b>Accessories</b><br><b>Acoustic insulation block</b> <sup>(19)</sup><br>For use when trunking passes through walls to reduce noise travel<br>Self extinguishing plastic<br>Acoustic tested according to NEN 5077/ISO 140/4 |
| 1    | MP351535  | <b>Cutting support block</b><br>Holds trunking in position and guides saw for a straight cut<br>Steel  |
| 1    | MP351029  | <b>Touch-up paint</b><br>Contents – 10 ml  |

1: Internal components supplied unpainted