

cavity floor grommets



Dimensions and technical information p. 31


Pack	Cat. Nos.	150 mm plastic grommets
1	SG6	Hole size 152 mm Carpet recess optional on power versions Secured by quarter-turn fasteners Access grommet Allows power, data and flexible conduit up to 32 mm to pass safely through raised access floor Maximum number of conduit entries : 9 x 20 mm Ø 5 x 25 mm Ø 3 x 32 mm Ø
1	PG6	13 A power grommet Supplied complete with 13 A unswitched socket
1	PG6RCD	RCD power grommet Supplied complete with 13 A RCD socket
1	PG6PD	13 A power/data grommet Supplied complete with 13 A socket and 1 x 37 x 22 mm cut-out
1	PG6D	Data grommet Supplied complete with data plate 2 x 37 x 22 mm cut-out



Pack	Cat. Nos.	125 mm aluminium grommets
1	0893 07	Hole size 127 mm Body – cast aluminium Lid – injection moulded plastic Nylon 66 with neoprene cable gasket Secured by quarter-turn fasteners Floor depth 25 to 55 mm Access grommet depth 60 mm (95 mm when back box included) Access grommet Allows power, data and flexible conduit up to 25 mm to pass safely through raised access floor
1	AM1B	13 A power grommet – unswitched Supplied complete with 13 A unswitched socket
1	AM1C	13 A power grommet – switched Supplied complete with 13 A switched socket



Pack	Cat. Nos.	250 mm grommet
1	LSG2	Hole size 250 mm Manufactured from polycarbonate/ABS Colour : grey to BS 4800 18B25 Secured by quarter-turn fasteners Floor depth 15 to 35 mm 7 mm lid recess Depth 55 mm Access grommet Allows power, data and flexible conduit up to 32 mm to pass safely through raised access floor



All power grommets are available pre-wired
Contact us on +44 (0) 370 608 9020