

equipment for Atlantic metal enclosures



0363 17



Cabstop plate Cat. No. 0364 97 and mounting kit Cat. No. 0364 98 on enclosure Cat. No. 0369 43



0347 95



0364 01



0364 04

Enclosure and equipment selection chart **p. 6-7**
 Technical information and dimensions **p. 13**

Pack	Cat. Nos.	Metallic internal doors		
		RAL 7035 For direct mounting in Atlantic metal and stainless steel enclosures IPXXB Reversible door with captive hinge pins Double bar lock Can be equipped with other key barrels and metal rebate locks. Distance between enclosure door and internal door: 55 mm		
		For enclosures (mm) Height x Width	Dimensions (mm) Height x Width	Usable dimensions (mm) Height x Width
1	0363 15	400 x 300	334 x 248	235 x 155
1	0363 16	500 x 400	434 x 348	335 x 255
1	0363 17	600 x 400	534 x 348	435 x 255
1	0363 18	700 x 500	634 x 448	535 x 355
1	0363 19	800 x 600	734 x 548	635 x 455
1	0363 20	1000 x 600	934 x 548	835 x 455
1	0363 21	1000 x 800	934 x 748	835 x 655
1	0363 22	1200 x 600	1134 x 548	1035 x 555
1	0363 23	1200 x 800	1134 x 748	1035 x 655

Pack	Cat. Nos.	Cabstop open-work plate IP 55			
		Cable entries consisting of a cable clamp providing the mechanical grip, and elastomer areas for weatherproofing Can be pierced using the cable (no tool required) Fits the cable perfectly Replacement of a cable possible Fire retardant polypropylene RAL 7035 2 possibilities of mounting: - direct on cable entry of Atlantic enclosures - on flat surface with kit Cat. No. 0364 98 Supplied with: - locking caps for sealing a pierced entry providing IP 55 protection - cable release tool			
		Number of entries Ø5 to 14	Number of entries Ø14 to 24	Number of spare entries	Direct mounting on cable entry of enclosure width (mm)
1	0364 94	13	1	-	300
1	0364 95	13	1	1	400
1	0364 96	28	2	1	500/1000
1	0364 97	28	2	2	600/800/1200
1	0364 98	Kit for mounting Cabstop plate on plain plate Enables mounting of 2 Cabstop plates: Cat. Nos. 0364 94 or 95 and 0364 96 or 97 IP 55 maintained			

Pack	Cat. Nos.	Protective conductor		
		Earth link		
		Capacity (mm ²)	Fixing spacing (mm)	Ø of holes (mm)
20	0347 95	6	200	8.5
20	0347 96	16	200	8.5
		Green/yellow wire		
20	0363 95	6	200	6.5
		Accessories		
		Wall mounting lugs (set of 4)		
1	0364 01	For load up to 300 kg Horizontal or vertical installation With a roof, horizontal installation only Zamak RAL 7035 Supplied with cover finish		
1	0364 04	For load up to 300 kg Horizontal or vertical installation Anti-corrosion steel treatment		