

## ventilation for enclosures



0348 17



0365 79



0348 04



0348 52



0348 89



0348 05



0348 35

### Technical information and dimensions p. 28

Pack	Cat. Nos.	Ventilation fan kit with metal grill
1	0348 17	<p>IP 32 - IK 10 230 V - 50/60 Hz RAL 7035 Ventilator is mounted on the outside of the enclosure 30 m<sup>3</sup>/h with filter - 160 m<sup>3</sup>/h without filter installed (free flowing) Pack comprising a pair of metal RAL 7035 louvres and a pair of anti-insect grills, plus internal finger protection</p>

Pack	Cat. Nos.	Ventilation fan kits with plastic grill
1	0348 50	<p>IP 54 - IK 08 230 V - 50/60 Hz RAL 7035 plastic housing Supplied with finger protection guards External projection 7-10 mm Accepts mounting spacer Cat. No. 0348 88/89 Used to reduce internal projection and improve wiring space Fitted externally on to the enclosure with rapid fix screws 1 mm to 4 mm panel thickness An extra louvre can be fitted to improve air flow and extraction</p> <p><b>40/160 m<sup>3</sup>/h</b> 40 m<sup>3</sup> with filter 45 m<sup>3</sup> with extra grill/filter Cat. No. 0348 34 160 m<sup>3</sup> without filter installed (free flowing) Pack comprising a pair of RAL 7035 plastic grills 150 x 150 mm and washable electrostatic filter EU3, G3</p>
1	0348 51	<p><b>120/160 m<sup>3</sup>/h</b> 120 m<sup>3</sup> with filter 130 m<sup>3</sup> with extra grill/filter Cat. No. 0348 35 160 m<sup>3</sup> without filter installed (free flowing) Pack comprising a pair of RAL 7035 plastic grills 250 x 250 mm and washable filter EU3, G3</p>
1	0348 52	<p><b>240/450 m<sup>3</sup>/h</b> 240 m<sup>3</sup> with filter 260 m<sup>3</sup> with extra grill/filter Cat. No. 0348 35 450 m<sup>3</sup> without filter installed (free flowing) Pack comprising a pair of RAL 7035 plastic grills 250 x 250 mm and washable filter EU3, G3</p>

Pack	Cat. Nos.	Spacers for ventilation fan kits
1	0348 88	IP 54 maintained
1	0348 89	<p>RAL 7035 Used to reduce the internal projection and increase the internal usable volume 150 x 150 mm 250 x 250 mm</p>

Pack	Cat. Nos.	Natural ventilation
2	0365 78	<b>Ventilation glands</b>
2	0365 79	<p>IP 44 - IK 08 for outdoor use Grey polyamide Ø 15 mm aperture needed Ø 30.5 mm aperture needed</p>
1	0348 04	<b>Ventilation louvres - metal</b>
1	0348 05	<p>IP 32 - IK 10 RAL 7035 Pack comprising a pair of metal louvres and a pair of anti-insect grills 138 x 138 mm 248 x 248 mm</p>
1	0348 34	<b>Ventilation louvres - plastic</b>
1	0348 35	<p>RAL 7035 Supplied singly Supplied with 10 mm thick filter EU 3, G3 IP 44 - 150 x 150 mm</p>
1	0348 36	<p>Supplied with 20 mm thick filter EU 3, G3 IP 54 - 250 x 250 mm IP 54 - 325 x 325 mm</p>

### Heating p. 29

