

Plexo weatherproof boxes

IP 55 - IK 07



0920 11



0359 40



Selection chart **p. 34**

Technical information and dimensions **p. 37**

IP 55 - IK 07

Grey RAL 7035

Conform to EN 60695-2-1

Temperature rating : - 25 °C to + 40 °C

Undrilled with smooth sides

Pack	Cat. Nos.	Weatherproof boxes – class II
		<p>Self-extinguishing 650 °C Polystyrene box and polypropylene cover - halogen free With fixing slots for easy alignment - use 5 mm Ø screws Clip-on plain cover</p> <p>Mounting by : • either internal fixing points - use 5 mm Ø screws • or at three corners outside the wiring area - use 4 mm Ø screws Provision for anti-tamper seal Cover with 4 x 1/4 turn fixings, indicated I-O, can be retained open during installation</p> <p>Nominal internal dimensions : Height x Width x Depth (mm)</p>
5	0920 11	80 x 80 x 45
5	0920 20	105 x 105 x 55

Pack	Cover		Cat. Nos.	Weatherproof boxes – class II
	Plain	Transparent		
1			0359 00	130 x 75 x 74
1			0359 30 ¹	130 x 130 x 74
1			0920 32	130 x 130 x 74 (10 membrane gland fitted for 4-25 mm cable or conduit)
1			0359 40 ¹	155 x 110 x 74
1			0920 42	155 x 110 x 74 (10 membrane gland fitted for 4-25 mm cable or conduit)
1			0359 50 ¹	180 x 140 x 86
1			0359 60 ¹	220 x 170 x 86
1			0359 70 ²	270 x 170 x 86
1			0359 80 ²	310 x 240 x 124
1			0359 90 ²	360 x 270 x 124
			0359 51 ¹	130 x 130 x 74
			0359 61 ¹	130 x 130 x 74
			0359 71 ²	130 x 130 x 74 (10 membrane gland fitted for 4-25 mm cable or conduit)

- 1 : Accepts Cat. No. 0358 00 hinges
2 : Accepts Cat. No. 0358 01 hinges
3 : Except Cat. No. 0359 80 : polycarbonate
4 : Not suitable for PVC range

Plexo weatherproof boxes

IP 66 - IK 08



0350 13



0350 28



0358 00



0358 02



Technical information and dimensions **p. 37**

Pack	Cat. Nos.	Weatherproof boxes – class II 500 V
		<p>IP 66 - IK 08 Grey TO 29 Conform to EN 60695-2-1 Temperature rating : - 25 °C to + 80 °C Undrilled with smooth sides Self-extinguishing 750 °C Polycarbonate - halogen free Detachable clip-on cover retainer (except for 310 x 240 and 360 x 270 mm boxes) Side mounts for IP 2X terminals provided (except for 130 x 75 x 74 mm boxes) Sealable plain cover with captive 1/4 turn fixings</p> <p>Nominal internal dimensions : Height x Width x Depth (mm)</p>
1	0350 07	130 x 75 x 74
1	0350 13 ¹	130 x 130 x 74
1	0350 17 ¹	155 x 110 x 74
1	0350 22 ¹	180 x 140 x 86
1	0350 28 ¹	220 x 170 x 86
1	0350 33 ²	270 x 170 x 86
1	0350 44 ²	310 x 240 x 124
1	0350 47 ²	360 x 270 x 124

Accessories		
Metal mounting plates		
Galvanised steel - 1.5 mm thick		
For box size :		
5	0358 10	130 x 130 mm
5	0358 11	155 x 110 mm
5	0358 12	180 x 140 mm
5	0358 13	220 x 170 mm
5	0358 14	270 x 170 mm
5	0358 15	310 x 240 mm
5	0358 16	360 x 270 mm
Set of 2 hinges⁴		
UV protected polyamide in dark grey (RAL 7016)		
1	0358 00	For box 130 x 130 mm to 270 x 170 mm
1	0358 01	For box 310 x 240 mm to 360 x 270 mm
Set of 4 wall mounting brackets		
For boxes from width 110 mm		
For wall fixing, supplied with screws		



Nylbloc terminal strips **p. 39**

Line taps **p. 39**

Distribution blocks **p. 40-43**

