

Colring® cable ties



0320 15/37/22/24

0320 42 supplied in blister pack

0320 65

0320 70

0320 72

0320 88

Technical information and dimensions **p. 76**

Pack Cat. Nos. Colring cable ties with internal teeth

With self-locking head
Conform to EN 62275 type 1 (NF C 68-146)

Polyamide 6/6 colourless

Blister packed

		Width (mm)	Flat length (mm)	Max. Ø grip capacity (mm)	Min. Ø grip capacity (mm)	Weight (g)
1000	0320 30	2-4	95	18	1-6	0-26
1000	0320 31	2-4	140	33	1-6	0-37
1000	0320 32	2-4	180	46	1-6	0-47
1000	0320 37	3-5	140	33	1-6	0-57
1000	0320 38	3-5	180	46	1-6	0-73
100	0320 39	3-5	280	77	1-6	1-13
100	0320 40	3-5	360	102	1-6	1-46
1000	0320 42	4-6	180	46	1-6	1-20
100	0320 43	4-6	280	77	1-6	1-88

Polyamide 6/6 black

High temperature
UV protected
Blister packed

		Width (mm)	Flat length (mm)	Max. Ø grip capacity (mm)	Min. Ø grip capacity (mm)	Weight (g)
100	0320 12	2-4	95	18	1-6	0-26
100	0320 15	3-5	140	33	1-6	0-57
1000	0320 22	4-6	180	46	1-6	1-20
100	0320 24	4-6	360	102	1-6	2-38

Accessories

Self-adhesive base

100 0320 65 For ties up to 4-6 mm max. width
Colourless

Screw mounting bases

1000 0320 70 For ties 4-6 mm max. width
Central fixing (screw Ø 4 mm)
100 0320 72 For ties all widths
Central fixing (screw Ø 5 mm)

Tool for Colring cable ties

1 0320 88 P 46 tool for cable ties
Max. width 4-6 mm
Direct adjustment of clamping tension by using the milled screw at the base of the handle
After clamping, a blade automatically cuts the surplus length close to the head without leaving a burr

Colson® cable ties



0319 16

0319 50

0319 55

0319 96

Technical information and dimensions **p. 77**

Pack Cat. Nos. Colson UV protected cable ties

Conform to EN 50146 and IEC 62275
UV protected
External teeth
Black polyamide 12

		Width (mm)	Flat length (mm)	Max. Ø grip capacity (mm)	Min. Ø grip capacity (mm)	Weight (g)
100	0319 13	9	185	42	10	3-2
100	0319 16	9	262	62	26	4-7
100	0319 19	9	357	92	26	6-9
100	0319 20	9	498	140	74	12-7
100	0319 21	9	750	220	74	16-9
100	0319 22	6	119	25	4	1-6
100	0319 25	6	180	45	10	2-0

Accessories

Screw-on base

100 0319 50 Black
For ties max. width 9 mm.
Height : 12 mm for cartridge-fired stud and rag-bolt
Ø 6-35 mm, metal stud Ø 7 mm and countersunk screws Ø 5 mm

Wall plug base

100 0319 55 Black
Ø 8 mm drilling

Tool for Colson cable ties

1 0319 96 Black and red finish
Allows tightening and trimming of Colson ties