

## Hypra® Prisinter IP 44/55 - LV 32 A

interlocked switched sockets



0529 13



Turn plug to lock in position and connect power



Press the isolator button to disconnect power and remove the plug



0529 04 + 0529 49

Technical information and dimensions **p. 86-87**  
Conformity to International Standards **p. 128**

Conform to BS EN 60309-1, BS EN 60309-2  
IP 44 when plug inserted  
IP 54 when used with IP 66/67-55 straight plugs  
IP 55 with cover closed or used with IP 66/67-55 angled plugs  
IK 09 (plastic)  
IK 10 (metal)  
Stainless steel screws  
Brass contacts

Pack	Cat. Nos.		Prisinter panel mounting sockets 32 A
			Load break disconnect at the push of the button Accepts Ø6 mm padlock with cover closed Terminals accept 2.5 mm <sup>2</sup> to 10 mm <sup>2</sup> rigid cable (BS EN 60309-1 and IEC 60309-1) Possibility to fit 2 auxiliary C/O contacts Cat. No. 0521 96
	Metal	Plastic	<b>200/250 V~</b>
1		0527 02	2 P + ⊥
1		0527 03	3 P + ⊥
			<b>380/415 V~</b>
1	0529 13	0529 03	3 P + ⊥
1	0529 14	0529 04	3 P + N + ⊥

Pack	Cat. Nos.		Surface mounting boxes
			Enable Hypra Prisinter panel mounting sockets to be surface mounted Reversible entry box with 2 x M25 and 1 x M20 entries with 1 x M25 and 1 x M20 blanking plugs plus rear knockout entries
1	Metal	Plastic	For 2 P + ⊥ / 3 P + ⊥ / 3 P + N + ⊥ sockets
	0522 59	0529 49	

IP 44 straight plugs **p. 90-92**



## Hypra® Prisinter IP 44/55 - LV 63 A

interlocked switched sockets



0538 00 + 0538 09



Turn plug to lock in position and connect power



Press the isolator button to disconnect power and remove the plug

Technical information and dimensions **p. 86-87**  
Conformity to International Standards **p. 128**

Conform to BS EN 60309-1, BS EN 60309-2  
IP 44 when plug inserted  
IP 54 when used with IP 66/67-55 straight plugs  
IP 55 with cover closed or used with IP 66/67-55 angled plugs  
IK 09 (plastic)  
IK 10 (metal)  
Stainless steel screws  
Brass contacts

Pack	Cat. Nos.		Prisinter panel mounting sockets 63 A
			Load break disconnect at the push of the button Accepts 3 x Ø8 mm padlocks with cover closed IP 2X protection against direct contact Terminals accept 6 mm <sup>2</sup> to 25 mm <sup>2</sup> rigid cable Possibility to fit 2 auxiliary C/O contacts Cat. No. 0521 96
	Metal	Plastic	<b>380/415 V~</b>
1	0538 00	0536 03	3 P + ⊥
1	0538 01	0536 04	3 P + N + ⊥

Pack	Cat. Nos.		Surface mounting boxes
			Enable Hypra Prisinter panel mounting sockets to be surface mounted Reversible entry box with 2 x M32 and 1 x M20 entries with 1 x M32 and 1 x M20 blanking plugs
1	Metal	Plastic	For 3 P + ⊥ / 3 P + N + ⊥ sockets
	0538 09	0537 49	

IP 66/67-55 angled and straight plugs **p. 97-98**

