

Hypra® IP 66/67-55 - LV 32 A

plastic plugs and sockets



0530 50 + 0529 40

Technical information and dimensions **p. 99-101**
Conformity to International Standards **p. 128**

Conform to BS EN 60309-1, BS 60309-2, IEC 60309-1 and IEC 60309-2
IP according to BS EN 60529 and IEC 60529

IK 09
Self-extinguishing : 850 °C for insulated parts, 650 °C for housing
Stainless steel external screws - Nickel plated brass contacts
Temp. rating : -50 °C to +100 °C

Pack Cat. Nos. Panel mounting sockets (modular) 32 A

Pack	Cat. Nos.	200 to 250 V~	380 to 415 V~
1	Modular 0530 46	2 P + ⊥	3 P + N + ⊥
1	0530 50	3 P + ⊥	
1	0530 51		3 P + N + ⊥

Mobile sockets 32 A

Pack	Cat. Nos.	200 to 250 V~	380 to 415 V~
1	0530 76	2 P + ⊥	3 P + N + ⊥
1	0530 80	3 P + ⊥	
1	0530 81		3 P + N + ⊥

Straight plugs 32 A

Pack	Cat. Nos.	200 to 250 V~	380 to 415 V~
1	0530 56	2 P + ⊥	3 P + N + ⊥
1	0530 60	3 P + ⊥	
1	0530 61		3 P + N + ⊥

Angled plugs 32 A

Pack	Cat. Nos.	200 to 250 V~	380 to 415 V~
1	0530 06	2 P + ⊥	3 P + N + ⊥
1	0530 10	3 P + ⊥	
1	0530 11		3 P + N + ⊥

Back boxes

Pack	Cat. Nos.	Surface mounting boxes	Through entry surface mounting boxes
1	0529 40	For LV 32 A 2 P + ⊥ / 3 P + ⊥ / 3 P + N + ⊥ sockets	
1	0529 90		For LV 32 A 2 P + ⊥ / 3 P + ⊥ / 3 P + N + ⊥ sockets

Hypra® IP 66/67-55 - LV 63 and 125 A

plastic plugs and sockets



0594 27



0595 32

Technical information and dimensions **p. 99-101**
Conformity to International Standards **p. 128**

Conform to BS EN 60309-1, BS 60309-2, IEC 60309-1 and IEC 60309-2
IP according to BS EN 60529 and IEC 60529

IK 09
Self-extinguishing : 850 °C for insulated parts, 650 °C for housing
Stainless steel external screws - Nickel plated brass contacts
Temp. rating : -50 °C to +100 °C
LV 63 A and 125 A have a pilot pin

Pack Cat. Nos. Panel mounting sockets 63 and 125 A

Pack	Cat. Nos.		380 to 415 V~
	63 A	125 A	
1	0594 27	0595 12	3 P + ⊥
1	0594 28	0595 13	3 P + N + ⊥

Surface mounting sockets 63 and 125 A

Pack	Cat. Nos.		380 to 415 V~
	63 A	125 A	
1	0594 37	0595 02	3 P + ⊥
1	0594 38	0595 03	3 P + N + ⊥

Mobile sockets 63 and 125 A

Pack	Cat. Nos.		380 to 415 V~
	63 A	125 A	
1	0594 87	0595 32	3 P + ⊥
1	0594 88	0595 33	3 P + N + ⊥

Straight plugs 63 and 125 A

Pack	Cat. Nos.		380 to 415 V~
	63 A	125 A	
1	0594 47	0595 22	3 P + ⊥
1	0594 48	0595 23	3 P + N + ⊥