

P 17 Tempra Pro IP 66/67 - LV 16 and 32 A

sockets, plugs, mobile sockets and appliance inlets



5554 14



5553 28

P 17 Tempra Pro IP 66/67/69¹ - LV 63 and 125 A

sockets, plugs, mobile sockets and appliance inlets and IP 66/67/69¹ LV 32 A for refrigerated containers



5555 59



Easy connection
disconnection

5555 09

Technical information and dimensions p. 110-112

Pack	Cat. Nos.		Surface mounting sockets
5	16 A 5553 51	32 A 5554 51	Two possible angles (5° or 25°) 100/130 V ~ 2 P + ⊥ 200/250 V ~ 2 P + ⊥ 5553 54 5554 54 2 P + ⊥ 5553 55 5554 55 3 P + ⊥ 5553 56 5554 56 3 P + N + ⊥ 380/415 V ~ 5553 58 5554 58 3 P + ⊥ 5553 59 5554 59 3 P + N + ⊥
5	16 A 5553 81	32 A -	Panel mounting sockets inclined outlet Can be fixed on faceplates (p. 18) 100/130 V ~ 2 P + ⊥ 200/250 V ~ 5553 84 5554 84 2 P + ⊥ 5553 85 5554 85 3 P + ⊥ 5553 86 5554 86 3 P + N + ⊥ 380/415 V ~ 5553 88 5554 88 3 P + ⊥ 5553 89 5554 89 3 P + N + ⊥
5	16 A 5553 01	32 A -	Mobile sockets Supplied unlocked 100/130 V ~ 2 P + ⊥ 200/250 V ~ 5553 04 5554 14 2 P + ⊥ 5553 05 5554 15 3 P + ⊥ 5553 06 5554 16 3 P + N + ⊥ 380/415 V ~ 5553 08 5554 18 3 P + ⊥ 5553 09 5554 19 3 P + N + ⊥
5	16 A 5553 21	32 A 5554 31	Straight plugs Supplied unlocked 100/130 V ~ 2 P + ⊥ 200/250 V ~ 5553 24 5554 34 2 P + ⊥ 5553 25 5554 35 3 P + ⊥ 5553 26 5554 36 3 P + N + ⊥ 380/415 V ~ 5553 28 5554 38 3 P + ⊥ 5553 29 5554 39 3 P + N + ⊥
5	16 A 0568 03	32 A 0568 23	Appliance inlets 200/250 V ~ 2 P + ⊥ 380/415 V ~ 0568 07 0568 27 3 P + ⊥ 0568 08 0568 28 3 P + N + ⊥

Technical information and dimensions p. 113-115

Pack	Cat. Nos.		Surface mounting sockets
2 2 2	63 A 5555 54 5555 55 5555 56	125 A - - -	200/250 V ~ 2 P + ⊥ 3 P + ⊥ 3 P + N + ⊥ 380/415 V ~ 2 1 5555 58 5556 58 3 P + ⊥ 2 1 5555 59 5556 59 3 P + N + ⊥
2 2 2	63 A 5555 84 5555 85 5555 86	125 A - - -	Panel mounting sockets inclined outlet Can be fixed on faceplates Cat. No. 0577 17 (p. 18) 200/250 V ~ 2 P + ⊥ 3 P + ⊥ 3 P + N + ⊥ 380/415 V ~ 2 1 5555 88 5556 88 3 P + ⊥ 2 1 5555 89 5556 89 3 P + N + ⊥
2 2 2	63 A 5555 04 5555 05 5555 06	125 A - - -	Mobile sockets 200/250 V ~ 2 P + ⊥ 3 P + ⊥ 3 P + N + ⊥ 380/415 V ~ 2 1 5555 08 5556 08 3 P + ⊥ 2 1 5555 09 5556 09 3 P + N + ⊥
2 2 2	63 A 5555 24 5555 25 5555 26	125 A - - -	Straight plugs 200/250 V ~ 2 P + ⊥ 3 P + ⊥ 3 P + N + ⊥ 380/415 V ~ 2 1 5555 28 5556 28 3 P + ⊥ 2 1 5555 29 5556 29 3 P + N + ⊥
2 2 1 2 1	63 A 5555 14 5555 18 5555 19	125 A - 5556 18 5556 19	Appliance inlets 200/250 V ~ 2 P + ⊥ 380/415 V ~ 3 P + ⊥ 3 P + N + ⊥

1: IP 69 available in 63 and 125 A in mobile sockets and straight plugs only