

Hypra® IP 66/67-55 combination units - LV 16/32/63/125 A

plastic surface mounting



0592 65



0591 15



0596 61

Technical information and dimensions **p. 121-122**
 Conformity to International Standards **p. 128**

Conform to BS EN 60309-1, BS EN 60309-2 and IEC 60309-1, IEC 60309-2
 IP 66/67-55 for 16 and 32 A and to BS EN 60529 and IEC 60529 for 63 and 125 A
 IK 09 conforms to BS EN 62262 and IEC 62262
 Temp. rating : -15 °C to +40 °C¹

Pack	Cat. Nos.		Single socket units with switch
	16 A	32 A	Double mechanical interlock
1	0592 60	0592 63	200 to 250 V~ 2 P + ⊥
			380 to 415 V~
1	0592 61	0592 64	3 P + ⊥
1	0592 62	0592 65	3 P + N + ⊥
	63 A		380 to 415 V~
1	0592 66		3 P + ⊥
1	0592 67		3 P + N + ⊥
	125 A		380 to 415 V~
1	0591 14 ²		3 P + ⊥
1	0591 15 ²		3 P + N + ⊥

Pack	Cat. Nos.		Single socket units with rail only, or complete with MCB 16/32 A
	16 A	32 A	Transparent plastic hinged viewing window Cable glands are not supplied (ISO) With 6 module DIN rail
1	0596 60		100 to 130 V~ rail only 2 P + ⊥
1	0596 61		200 to 250 V~ with MCB 2 P + ⊥
			380 to 415 V~ with MCB
1		0596 67	3 P + ⊥
1		0596 68	3 P + N + ⊥

Pack	Cat. Nos.		Single socket units with switch and protected by 30 mA RCBO or RCD
	16 A	32 A	Transparent plastic hinged viewing window Cable glands are not supplied (ISO) With 6 module DIN rail
1	0596 51	0596 55	200 to 250 V~ with RCBO 2 P + ⊥
			380 to 415 V~ with RCBO
1	0596 52	0596 57	3 P + ⊥
1	0596 53	0596 58	3 P + N + ⊥
	63 A		380 to 415 V~ with RCD
1	0596 81		3 P + N + ⊥

1 : Units with RCBO and some MCB protection devices have temperature ratings of -5 °C to +40 °C
 Switch only units and some MCBs have increased ratings - contact us on +44 (0) 345 605 4333
 2 : Interlocked using a Vistop switch - contact us on +44 (0) 345 605 4333

